

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253655

Luminaire Tested: P3AS02R609035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253655
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 101.0 lumens
Efficiency: N/A
Efficacy: 28.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253655

CATALOG NUMBER: P3AS02R609035DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1253655

CATALOG NUMBER: P3AS02R609035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	91	82	76	71	80	75	71		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17937
5°	17720
10°	17123
15°	16164
20°	14911
25°	13501
30°	11977
35°	10226
40°	8130
45°	5737
50°	3446
55°	1720
60°	1667
65°	1505
70°	1410
75°	1356
80°	1263
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5737 cd/sqm

TEST NUMBER: P1253655

CATALOG NUMBER: P3AS02R609035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.6	7.5
10°-20°	19.9	19.7
20°-30°	25.6	25.3
30°-40°	23.7	23.5
40°-50°	14.4	14.3
50°-60°	4.8	4.8
60°-70°	2.9	2.9
70°-80°	1.6	1.6
80°-90°	0.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	53.0	52.5
0°-40°	76.7	76.0
0°-60°	95.9	95.0
0°-90°	101.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	101.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	82	
5°	80	8
15°	71	20
25°	56	26
35°	38	24
45°	18	14
55°	4	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1253655

CATALOG NUMBER: P3AS02R609035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	81.8
2.5°	81.4
5°	80.5
7.5°	78.9
10°	76.9
12.5°	74.3
15°	71.2
17.5°	67.7
20°	63.9
22.5°	59.8
25°	55.8
27.5°	51.6
30°	47.3
32.5°	43.0
35°	38.2
37.5°	33.2
40°	28.4
42.5°	23.4
45°	18.5
47.5°	14.3
50°	10.1
52.5°	6.0
55°	4.5
57.5°	4.2
60°	3.8
62.5°	3.3
65°	2.9
67.5°	2.6
70°	2.2
72.5°	1.8
75°	1.6
77.5°	1.2
80°	1.0
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)