

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254635

Luminaire Tested: P3AS13R259035DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259035DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 513.0 lumens
Efficiency: N/A
Efficacy: 35.1 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254635

CATALOG NUMBER: P3AS13R259035DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254635

CATALOG NUMBER: P3AS13R259035DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	329075
5°	307021
10°	245954
15°	166948
20°	101019
25°	59060
30°	33651
35°	18498
40°	9818
45°	5179
50°	3002
55°	2256
60°	1930
65°	2024
70°	1859
75°	1694
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5179 cd/sqm

TEST NUMBER: P1254635

CATALOG NUMBER: P3AS13R259035DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	24.1
10°-20°	202.2	39.4
20°-30°	115.5	22.5
30°-40°	45.6	8.9
40°-50°	14.0	2.7
50°-60°	5.5	1.1
60°-70°	3.7	0.7
70°-80°	2.1	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.5	86.1
0°-40°	487.1	94.9
0°-60°	506.6	98.7
0°-90°	513.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	513.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1501	
5°	1395	124
15°	735	202
25°	244	116
35°	69	46
45°	17	14
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1254635

CATALOG NUMBER: P3AS13R259035DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1500.7
1°	1497.7
2°	1485.5
3°	1463.9
4°	1434.0
5°	1394.8
6°	1348.7
7°	1296.7
8°	1236.4
9°	1174.7
10°	1104.6
11°	1035.4
12°	959.4
13°	884.4
14°	807.5
15°	735.4
17.5°	570.2
20°	432.9
22.5°	325.0
25°	244.1
27.5°	180.9
30°	132.9
32.5°	96.1
35°	69.1
37.5°	49.0
40°	34.3
42.5°	23.5
45°	16.7
47.5°	11.8
50°	8.8
52.5°	6.9
55°	5.9
57.5°	5.4
60°	4.4
62.5°	3.9
65°	3.9
67.5°	3.4
70°	2.9
72.5°	2.5
75°	2.0
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5



TEST NUMBER: P1254635

CATALOG NUMBER: P3AS13R259035DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)