

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253657

Luminaire Tested: P3AS02R609035DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609035DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 207.0 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253657

CATALOG NUMBER: P3AS02R609035DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1253657

CATALOG NUMBER: P3AS02R609035DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61		
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44		
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36751
5°	36342
10°	35069
15°	33144
20°	30546
25°	27655
30°	24561
35°	20987
40°	16688
45°	11753
50°	7027
55°	3555
60°	3421
65°	3113
70°	2885
75°	2796
80°	2526
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11753 cd/sqm

TEST NUMBER: P1253657

CATALOG NUMBER: P3AS02R609035DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.5	7.5
10°-20°	40.8	19.7
20°-30°	52.4	25.3
30°-40°	48.6	23.5
40°-50°	29.6	14.3
50°-60°	9.8	4.8
60°-70°	6.0	2.9
70°-80°	3.4	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	108.7	52.5
0°-40°	157.3	76.0
0°-60°	196.7	95.0
0°-90°	207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	168	
5°	165	16
15°	146	41
25°	114	52
35°	78	49
45°	38	30
55°	9	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1253657

CATALOG NUMBER: P3AS02R609035DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	167.6
2.5°	166.8
5°	165.1
7.5°	161.8
10°	157.5
12.5°	152.2
15°	146.0
17.5°	138.7
20°	130.9
22.5°	122.6
25°	114.3
27.5°	105.8
30°	97.0
32.5°	88.2
35°	78.4
37.5°	68.1
40°	58.3
42.5°	48.0
45°	37.9
47.5°	29.4
50°	20.6
52.5°	12.3
55°	9.3
57.5°	8.5
60°	7.8
62.5°	6.8
65°	6.0
67.5°	5.3
70°	4.5
72.5°	3.8
75°	3.3
77.5°	2.5
80°	2.0
82.5°	1.3
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)