

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253670

Luminaire Tested: P3AS02R659035DE010 E3CD1MB

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1253670  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R659035DE010 E3CD1MB  
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 310.1 lumens  
Efficiency: N/A  
Efficacy: 86.1 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253670

CATALOG NUMBER: P3AS02R659035DE010 E3CD1MB

### Luminous Intensity Polar Plot



TEST NUMBER: P1253670

CATALOG NUMBER: P3AS02R659035DE010 E3CD1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 93  |    |    |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 95  | 98  | 95  | 93  | 95  | 93  | 91  | 92  | 90  | 89  | 87  |    |    |
| 3   | 103 | 96  | 91  | 87  | 101 | 95  | 90  | 87  | 92  | 88  | 85  | 90  | 87  | 84  | 87  | 85  | 83  | 81  |    |    |
| 4   | 97  | 90  | 84  | 80  | 96  | 89  | 84  | 80  | 87  | 82  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 75  |    |    |
| 5   | 93  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  | 80  | 76  | 72  | 78  | 75  | 72  | 70  |    |    |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 69  | 77  | 72  | 68  | 75  | 71  | 68  | 74  | 70  | 67  | 66  |    |    |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 63  | 70  | 66  | 63  | 62  |    |    |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 64  | 60  | 68  | 63  | 60  | 67  | 63  | 59  | 66  | 62  | 59  | 58  |    |    |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  | 64  | 59  | 56  | 63  | 59  | 56  | 54  |    |    |
| 10  | 72  | 62  | 57  | 53  | 71  | 62  | 57  | 53  | 61  | 56  | 53  | 60  | 56  | 52  | 60  | 55  | 52  | 51  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 75761 |
| 5°  | 71296 |
| 10° | 70384 |
| 15° | 69149 |
| 20° | 65292 |
| 25° | 60608 |
| 30° | 47096 |
| 35° | 27251 |
| 40° | 10992 |
| 45° | 5055  |
| 50° | 1979  |
| 55° | 765   |
| 60° | 658   |
| 65° | 675   |
| 70° | 641   |
| 75° | 678   |
| 80° | 631   |
| 85° | 755   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 5055 cd/sqm

TEST NUMBER: P1253670

CATALOG NUMBER: P3AS02R659035DE010 E3CD1MB

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 30.8   | 9.9       |
| 10°-20°   | 85.1   | 27.4      |
| 20°-30°   | 111.4  | 35.9      |
| 30°-40°   | 64.5   | 20.8      |
| 40°-50°   | 13.8   | 4.5       |
| 50°-60°   | 2.3    | 0.7       |
| 60°-70°   | 1.2    | 0.4       |
| 70°-80°   | 0.8    | 0.2       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 227.2  | 73.3      |
| 0°-40°    | 291.7  | 94.1      |
| 0°-60°    | 307.8  | 99.3      |
| 0°-90°    | 310.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 310.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 346 |      |
| 5°  | 324 | 31   |
| 15° | 305 | 85   |
| 25° | 250 | 111  |
| 35° | 102 | 65   |
| 45° | 16  | 14   |
| 55° | 2   | 2    |
| 65° | 1   | 1    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1253670

CATALOG NUMBER: P3AS02R659035DE010 E3CD1MB

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 345.5 |
| 2.5°  | 335.7 |
| 5°    | 323.9 |
| 7.5°  | 319.2 |
| 10°   | 316.1 |
| 12.5° | 311.9 |
| 15°   | 304.6 |
| 17.5° | 293.3 |
| 20°   | 279.8 |
| 22.5° | 267.0 |
| 25°   | 250.5 |
| 27.5° | 222.6 |
| 30°   | 186.0 |
| 32.5° | 144.2 |
| 35°   | 101.8 |
| 37.5° | 64.4  |
| 40°   | 38.4  |
| 42.5° | 24.1  |
| 45°   | 16.3  |
| 47.5° | 10.5  |
| 50°   | 5.8   |
| 52.5° | 2.8   |
| 55°   | 2.0   |
| 57.5° | 1.8   |
| 60°   | 1.5   |
| 62.5° | 1.5   |
| 65°   | 1.3   |
| 67.5° | 1.0   |
| 70°   | 1.0   |
| 72.5° | 0.8   |
| 75°   | 0.8   |
| 77.5° | 0.5   |
| 80°   | 0.5   |
| 82.5° | 0.3   |
| 85°   | 0.3   |
| 87.5° | 0.3   |
| 90°   | 0.0   |

(END OF REPORT)