

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254683

Luminaire Tested: P3AS13R309035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1059.0 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254683

CATALOG NUMBER: P3AS13R309035DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1254683

CATALOG NUMBER: P3AS13R309035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	617955
5°	588178
10°	494736
15°	356778
20°	221313
25°	125862
30°	69909
35°	38039
40°	20038
45°	10854
50°	5799
55°	3823
60°	3508
65°	3632
70°	3206
75°	2542
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10854 cd/sqm

TEST NUMBER: P1254683

CATALOG NUMBER: P3AS13R309035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.6	22.7
10°-20°	427.7	40.4
20°-30°	247.2	23.3
30°-40°	93.8	8.9
40°-50°	28.8	2.7
50°-60°	9.7	0.9
60°-70°	6.6	0.6
70°-80°	3.6	0.3
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	915.5	86.5
0°-40°	1009.3	95.3
0°-60°	1047.8	98.9
0°-90°	1059.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1059.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2818	
5°	2672	241
15°	1572	428
25°	520	247
35°	142	94
45°	35	29
55°	10	10
65°	7	7
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1254683

CATALOG NUMBER: P3AS13R309035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2818.1
1°	2816.1
2°	2799.1
3°	2767.1
4°	2727.1
5°	2672.1
6°	2602.0
7°	2524.0
8°	2437.0
9°	2332.9
10°	2221.9
11°	2101.8
12°	1974.8
13°	1841.7
14°	1706.7
15°	1571.6
17.5°	1239.5
20°	948.4
22.5°	703.3
25°	520.2
27.5°	378.2
30°	276.1
32.5°	199.1
35°	142.1
37.5°	99.0
40°	70.0
42.5°	49.0
45°	35.0
47.5°	24.0
50°	17.0
52.5°	12.0
55°	10.0
57.5°	9.0
60°	8.0
62.5°	7.0
65°	7.0
67.5°	6.0
70°	5.0
72.5°	4.0
75°	3.0
77.5°	3.0
80°	2.0
82.5°	2.0
85°	1.0
87.5°	0.0



TEST NUMBER: P1254683

CATALOG NUMBER: P3AS13R309035DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)