

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254692

Luminaire Tested: P3AS13R359035DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254692
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359035DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1270.0 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254692

CATALOG NUMBER: P3AS13R359035DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1254692

CATALOG NUMBER: P3AS13R359035DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	110	109	107		106	105	104		103	102	101		99	99	98
2	111	107	104	101		109	105	103	100		102	100	98		99	98	96		97	95	94
3	107	102	98	95		105	101	97	95		98	96	93		96	94	92		94	92	90
4	104	98	94	91		102	97	93	90		95	92	89		93	90	88		91	89	87
5	100	94	90	87		99	93	89	86		92	88	86		90	87	85		89	86	84
6	97	91	86	83		96	90	86	83		89	85	82		87	84	82		86	83	81
7	94	87	83	80		93	87	83	80		86	82	79		85	81	79		84	81	79
8	91	84	80	77		90	84	80	77		83	79	77		82	79	76		81	78	76
9	89	82	77	74		88	81	77	74		80	77	74		80	76	74		79	76	74
10	86	79	75	72		85	79	75	72		78	74	72		77	74	72		77	74	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	828113
5°	811246
10°	754718
15°	553329
20°	283338
25°	102127
30°	39753
35°	13920
40°	5725
45°	1551
50°	1365
55°	1529
60°	1316
65°	1038
70°	1282
75°	1694
80°	1263
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 1694 cd/sqm

TEST NUMBER: P1254692

CATALOG NUMBER: P3AS13R359035DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.6	27.1
10°-20°	644.7	50.8
20°-30°	228.2	18.0
30°-40°	40.0	3.1
40°-50°	5.8	0.5
50°-60°	3.2	0.3
60°-70°	2.3	0.2
70°-80°	1.7	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1216.5	95.8
0°-40°	1256.4	98.9
0°-60°	1265.5	99.6
0°-90°	1270.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1270.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3776	
5°	3686	344
15°	2437	645
25°	422	228
35°	52	40
45°	5	6
55°	4	3
65°	2	2
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1254692

CATALOG NUMBER: P3AS13R359035DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3776.5
1°	3775.5
2°	3763.5
3°	3740.5
4°	3719.5
5°	3685.5
6°	3650.5
7°	3611.5
8°	3563.5
9°	3488.5
10°	3389.5
11°	3252.5
12°	3087.4
13°	2891.4
14°	2675.4
15°	2437.4
17.5°	1815.3
20°	1214.2
22.5°	732.1
25°	422.1
27.5°	252.0
30°	157.0
32.5°	91.0
35°	52.0
37.5°	33.0
40°	20.0
42.5°	10.0
45°	5.0
47.5°	4.0
50°	4.0
52.5°	4.0
55°	4.0
57.5°	3.0
60°	3.0
62.5°	3.0
65°	2.0
67.5°	2.0
70°	2.0
72.5°	2.0
75°	2.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1254692
CATALOG NUMBER: P3AS13R359035DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)