

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253684

Luminaire Tested: P3AS02R659035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 97.0 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253684

CATALOG NUMBER: P3AS02R659035DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1253684

CATALOG NUMBER: P3AS02R659035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17257
5°	17037
10°	16455
15°	15528
20°	14305
25°	12993
30°	11521
35°	9798
40°	7786
45°	5489
50°	3207
55°	1759
60°	1623
65°	1453
70°	1346
75°	1271
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5489 cd/sqm

TEST NUMBER: P1253684

CATALOG NUMBER: P3AS02R659035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.3	7.5
10°-20°	19.1	19.7
20°-30°	24.6	25.3
30°-40°	22.7	23.5
40°-50°	13.7	14.1
50°-60°	4.7	4.8
60°-70°	2.8	2.9
70°-80°	1.6	1.6
80°-90°	0.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	51.0	52.6
0°-40°	73.7	76.0
0°-60°	92.1	95.0
0°-90°	97.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	97.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	79	
5°	77	7
15°	68	19
25°	54	25
35°	37	23
45°	18	14
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1253684

CATALOG NUMBER: P3AS02R659035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	78.7
2.5°	78.3
5°	77.4
7.5°	75.9
10°	73.9
12.5°	71.5
15°	68.4
17.5°	65.0
20°	61.3
22.5°	57.5
25°	53.7
27.5°	49.6
30°	45.5
32.5°	41.3
35°	36.6
37.5°	32.0
40°	27.2
42.5°	22.4
45°	17.7
47.5°	13.4
50°	9.4
52.5°	5.9
55°	4.6
57.5°	4.1
60°	3.7
62.5°	3.2
65°	2.8
67.5°	2.5
70°	2.1
72.5°	1.8
75°	1.5
77.5°	1.2
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)