

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254722

Luminaire Tested: P3AS13R409035DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409035DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1400.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254722
CATALOG NUMBER: P3AS13R409035DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1254722
 CATALOG NUMBER: P3AS13R409035DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96			96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92			92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88			88
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85			85
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82			82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79			79
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76			76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73			73
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70			70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	713605
5°	708473
10°	689923
15°	616281
20°	408649
25°	153081
30°	40943
35°	16008
40°	5754
45°	2729
50°	853
55°	382
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2729 cd/sqm



TEST NUMBER: P1254722
 CATALOG NUMBER: P3AS13R409035DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.7	21.7
10°-20°	719.3	51.4
20°-30°	326.2	23.3
30°-40°	42.3	3.0
40°-50°	7.3	0.5
50°-60°	0.9	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1349.2	96.4
0°-40°	1391.5	99.4
0°-60°	1399.7	100.0
0°-90°	1400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1400.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3254	
5°	3219	304
15°	2715	719
25°	633	326
35°	60	42
45°	9	7
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1254722
CATALOG NUMBER: P3AS13R409035DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3254.3
1°	3252.4
2°	3247.5
3°	3240.1
4°	3230.8
5°	3218.6
6°	3204.3
7°	3186.7
8°	3165.1
9°	3135.7
10°	3098.5
11°	3054.9
12°	2996.5
13°	2924.5
14°	2830.4
15°	2714.7
16°	2567.2
17°	2399.1
18°	2197.2
19°	1984.0
20°	1751.2
21°	1518.4
22°	1289.0
23°	1060.6
24°	836.1
25°	632.7
26°	468.5
27°	343.1
28°	257.8
29°	200.5
30°	161.7
31°	133.8
32°	111.7
32.5°	101.9
33°	92.1
34°	75.0
35°	59.8
36°	47.1
37°	37.2
37.5°	33.3
38°	29.4
39°	24.5
40°	20.1
42.5°	13.2
45°	8.8



TEST NUMBER: P1254722
CATALOG NUMBER: P3AS13R409035DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	5.4
50°	2.5
52.5°	1.0
55°	1.0
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)