

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253704

Luminaire Tested: P3AS02R709035DE010 E3D1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1253704  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R709035DE010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 314.1 lumens  
Efficiency: N/A  
Efficacy: 87.2 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253704  
CATALOG NUMBER: P3AS02R709035DE010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1253704  
 CATALOG NUMBER: P3AS02R709035DE010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    | 100 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 96  | 94  | 93  |    |    | 93  |
| 2   | 107 | 102 | 97  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  | 94  | 91  | 89  | 91  | 89  | 87  | 85  |    |    | 85  |
| 3   | 101 | 94  | 89  | 85  | 99  | 93  | 88  | 84  | 90  | 86  | 83  | 88  | 84  | 81  | 85  | 82  | 80  | 78  |    |    | 78  |
| 4   | 95  | 87  | 81  | 77  | 94  | 86  | 81  | 76  | 84  | 79  | 75  | 82  | 78  | 75  | 80  | 77  | 74  | 72  |    |    | 72  |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  | 77  | 72  | 69  | 75  | 71  | 68  | 66  |    |    | 66  |
| 6   | 85  | 75  | 69  | 64  | 83  | 75  | 69  | 64  | 73  | 68  | 64  | 72  | 67  | 63  | 70  | 66  | 63  | 61  |    |    | 61  |
| 7   | 80  | 70  | 64  | 59  | 79  | 70  | 64  | 59  | 68  | 63  | 59  | 67  | 62  | 59  | 66  | 62  | 58  | 57  |    |    | 57  |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 55  | 63  | 58  | 54  | 62  | 57  | 54  | 53  |    |    | 53  |
| 9   | 72  | 62  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  | 59  | 54  | 50  | 58  | 54  | 50  | 49  |    |    | 49  |
| 10  | 68  | 58  | 52  | 47  | 67  | 57  | 51  | 47  | 56  | 51  | 47  | 56  | 51  | 47  | 55  | 50  | 47  | 46  |    |    | 46  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 62341 |
| 5°  | 59498 |
| 10° | 56601 |
| 15° | 55097 |
| 20° | 53065 |
| 25° | 50229 |
| 30° | 46716 |
| 35° | 39244 |
| 40° | 25276 |
| 45° | 11753 |
| 50° | 3070  |
| 55° | 765   |
| 60° | 789   |
| 65° | 675   |
| 70° | 641   |
| 75° | 678   |
| 80° | 631   |
| 85° | 755   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11753 cd/sqm



TEST NUMBER: P1253704  
 CATALOG NUMBER: P3AS02R709035DE010 E3D1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 25.3   | 8.1       |
| 10°-20°   | 68.2   | 21.7      |
| 20°-30°   | 95.3   | 30.3      |
| 30°-40°   | 88.3   | 28.1      |
| 40°-50°   | 31.7   | 10.1      |
| 50°-60°   | 2.7    | 0.9       |
| 60°-70°   | 1.4    | 0.4       |
| 70°-80°   | 0.9    | 0.3       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 188.8  | 60.1      |
| 0°-40°    | 277.1  | 88.2      |
| 0°-60°    | 311.5  | 99.2      |
| 0°-90°    | 314.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 314.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 284 |      |
| 5°  | 270 | 25   |
| 15° | 243 | 68   |
| 25° | 208 | 95   |
| 35° | 147 | 88   |
| 45° | 38  | 32   |
| 55° | 2   | 3    |
| 65° | 1   | 1    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P1253704  
CATALOG NUMBER: P3AS02R709035DE010 E3D1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 284.3 |
| 2.5°  | 280.1 |
| 5°    | 270.3 |
| 7.5°  | 261.3 |
| 10°   | 254.2 |
| 12.5° | 248.5 |
| 15°   | 242.7 |
| 17.5° | 235.7 |
| 20°   | 227.4 |
| 22.5° | 217.8 |
| 25°   | 207.6 |
| 27.5° | 197.0 |
| 30°   | 184.5 |
| 32.5° | 168.4 |
| 35°   | 146.6 |
| 37.5° | 118.7 |
| 40°   | 88.3  |
| 42.5° | 60.2  |
| 45°   | 37.9  |
| 47.5° | 21.1  |
| 50°   | 9.0   |
| 52.5° | 3.0   |
| 55°   | 2.0   |
| 57.5° | 1.8   |
| 60°   | 1.8   |
| 62.5° | 1.5   |
| 65°   | 1.3   |
| 67.5° | 1.3   |
| 70°   | 1.0   |
| 72.5° | 1.0   |
| 75°   | 0.8   |
| 77.5° | 0.8   |
| 80°   | 0.5   |
| 82.5° | 0.5   |
| 85°   | 0.3   |
| 87.5° | 0.3   |
| 90°   | 0.0   |

(END OF REPORT)