

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253706

Luminaire Tested: P3AS02R709035DE010 E3D1WMH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1253706  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R709035DE010 E3D1WMH  
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 298.9 lumens  
Efficiency: N/A  
Efficacy: 83.0 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253706  
CATALOG NUMBER: P3AS02R709035DE010 E3D1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1253706  
 CATALOG NUMBER: P3AS02R709035DE010 E3D1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79
4	95	87	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			57
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	58131
5°	54809
10°	51970
15°	51056
20°	49214
25°	46382
30°	46058
35°	40100
40°	25934
45°	12249
50°	1706
55°	153
60°	88
65°	104
70°	64
75°	85
80°	126
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12249 cd/sqm



TEST NUMBER: P1253706  
 CATALOG NUMBER: P3AS02R709035DE010 E3D1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.3	7.8
10°-20°	63.2	21.1
20°-30°	89.3	29.9
30°-40°	89.8	30.0
40°-50°	32.3	10.8
50°-60°	0.9	0.3
60°-70°	0.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	175.7	58.8
0°-40°	265.5	88.8
0°-60°	298.6	99.9
0°-90°	298.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	298.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	265	
5°	249	23
15°	225	63
25°	192	89
35°	150	90
45°	40	32
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1253706  
CATALOG NUMBER: P3AS02R709035DE010 E3D1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	265.1
1°	264.4
2°	262.1
3°	258.4
4°	253.7
5°	249.0
6°	244.6
7°	241.2
8°	238.1
9°	235.7
10°	233.4
11°	231.6
12°	229.9
13°	228.2
14°	226.6
15°	224.9
16°	222.8
17°	220.6
18°	217.9
19°	214.5
20°	210.9
21°	206.8
22°	202.7
23°	198.8
24°	195.0
25°	191.7
26°	189.4
27°	187.5
28°	186.0
29°	184.3
30°	181.9
31°	178.3
32°	173.3
32.5°	170.5
33°	166.6
34°	159.2
35°	149.8
36°	139.5
37°	127.8
37.5°	122.4
38°	115.1
39°	101.9
40°	90.6
42.5°	62.8
45°	39.5



TEST NUMBER: P1253706  
CATALOG NUMBER: P3AS02R709035DE010 E3D1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	21.2
50°	5.0
52.5°	0.6
55°	0.4
57.5°	0.4
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.1
77.5°	0.1
80°	0.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)