

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254739

Luminaire Tested: P3AS13R409035DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254739
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409035DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 360.0 lumens
Efficiency: N/A
Efficacy: 24.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254739

CATALOG NUMBER: P3AS13R409035DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254739

CATALOG NUMBER: P3AS13R409035DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112096
5°	109817
10°	102247
15°	89127
20°	71826
25°	53834
30°	37854
35°	24788
40°	15000
45°	8962
50°	5356
55°	4320
60°	3859
65°	3321
70°	3142
75°	2457
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8962 cd/sqm

TEST NUMBER: P1254739

CATALOG NUMBER: P3AS13R409035DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.3	12.9
10°-20°	108.1	30.0
20°-30°	101.9	28.3
30°-40°	58.9	16.4
40°-50°	23.5	6.5
50°-60°	10.4	2.9
60°-70°	6.4	1.8
70°-80°	3.4	0.9
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.4	71.2
0°-40°	315.3	87.6
0°-60°	349.1	97.0
0°-90°	360.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	360.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	511	
5°	499	46
15°	393	108
25°	222	102
35°	93	59
45°	29	23
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1254739

CATALOG NUMBER: P3AS13R409035DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	511.2
2.5°	508.3
5°	498.9
7.5°	481.8
10°	459.2
12.5°	428.9
15°	392.6
17.5°	351.9
20°	307.8
22.5°	263.7
25°	222.5
27.5°	184.3
30°	149.5
32.5°	119.1
35°	92.6
37.5°	70.1
40°	52.4
42.5°	39.2
45°	28.9
47.5°	21.1
50°	15.7
52.5°	12.7
55°	11.3
57.5°	10.3
60°	8.8
62.5°	7.4
65°	6.4
67.5°	5.4
70°	4.9
72.5°	3.9
75°	2.9
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)