

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253738

Luminaire Tested: P3AS05R109035DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253738
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R109035DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R10 optic, 3500K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 468.1 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253738

CATALOG NUMBER: P3AS05R109035DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1253738

CATALOG NUMBER: P3AS05R109035DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	399793
5°	354875
10°	246444
15°	145744
20°	83004
25°	47446
30°	26257
35°	14000
40°	7757
45°	4186
50°	2627
55°	2064
60°	1798
65°	1660
70°	1475
75°	1525
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4186 cd/sqm

TEST NUMBER: P1253738

CATALOG NUMBER: P3AS05R109035DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.1	29.3
10°-20°	180.9	38.7
20°-30°	93.2	19.9
30°-40°	35.0	7.5
40°-50°	11.5	2.4
50°-60°	4.9	1.1
60°-70°	3.1	0.7
70°-80°	1.9	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	411.2	87.8
0°-40°	446.2	95.3
0°-60°	462.5	98.8
0°-90°	468.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	468.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1823	
5°	1612	137
15°	642	181
25°	196	93
35°	52	35
45°	14	11
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1253738

CATALOG NUMBER: P3AS05R109035DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1823.2
1°	1819.6
2°	1795.7
3°	1750.2
4°	1690.2
5°	1612.2
6°	1523.9
7°	1426.9
8°	1319.2
9°	1212.8
10°	1106.8
12.5°	851.6
15°	642.0
17.5°	480.6
20°	355.7
22.5°	265.5
25°	196.1
27.5°	142.9
30°	103.7
32.5°	73.5
35°	52.3
37.5°	37.4
40°	27.1
42.5°	19.4
45°	13.5
47.5°	9.9
50°	7.7
52.5°	6.3
55°	5.4
57.5°	4.5
60°	4.1
62.5°	3.6
65°	3.2
67.5°	2.7
70°	2.3
72.5°	2.3
75°	1.8
77.5°	1.4
80°	0.9
82.5°	0.9
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)