

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254748

Luminaire Tested: P3AS13R459035DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254748
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459035DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1341.0 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254748
CATALOG NUMBER: P3AS13R459035DE010 E3CD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1254748

CATALOG NUMBER: P3AS13R459035DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	581401
5°	584502
10°	566545
15°	474759
20°	362912
25°	220924
30°	91938
35°	29446
40°	9160
45°	1861
50°	1365
55°	1529
60°	1316
65°	1557
70°	1282
75°	1694
80°	1263
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1861 cd/sqm



TEST NUMBER: P1254748
 CATALOG NUMBER: P3AS13R459035DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.4	18.7
10°-20°	574.8	42.9
20°-30°	413.9	30.9
30°-40°	86.1	6.4
40°-50°	7.9	0.6
50°-60°	3.2	0.2
60°-70°	2.6	0.2
70°-80°	1.7	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1239.1	92.4
0°-40°	1325.2	98.8
0°-60°	1336.3	99.6
0°-90°	1341.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1341.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2651	
5°	2655	250
15°	2091	575
25°	913	414
35°	110	86
45°	6	8
55°	4	3
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1254748
CATALOG NUMBER: P3AS13R459035DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2651.4
2.5°	2652.4
5°	2655.4
7.5°	2636.4
10°	2544.4
12.5°	2352.3
15°	2091.3
17.5°	1824.3
20°	1555.2
22.5°	1246.2
25°	913.1
27.5°	602.1
30°	363.1
32.5°	203.0
35°	110.0
37.5°	62.0
40°	32.0
42.5°	14.0
45°	6.0
47.5°	4.0
50°	4.0
52.5°	4.0
55°	4.0
57.5°	3.0
60°	3.0
62.5°	3.0
65°	3.0
67.5°	2.0
70°	2.0
72.5°	2.0
75°	2.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)