

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253742

Luminaire Tested: P3AS05R109035DE010 E3DLD1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1253742  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R109035DE010 E3DLD1LI  
Description: 3in Adjustable LED luminaire with, R10 optic, 3500K CCT AND, 90CRI , E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 356.1 lumens  
Efficiency: N/A  
Efficacy: 45.1 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253742

CATALOG NUMBER: P3AS05R109035DE010 E3DLD1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1253742

CATALOG NUMBER: P3AS05R109035DE010 E3DLD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 100 |
| 1   | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 91  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 95  | 91  | 95  | 92  | 89  |  | 92  | 90  | 87  |  | 83  |
| 3   | 100 | 93  | 87  | 83  | 98  | 91  | 86  | 82  | 89  | 84  | 81  |  | 86  | 82  | 79  |  | 76  |
| 4   | 94  | 86  | 80  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  |  | 80  | 76  | 73  |  | 70  |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 72  | 67  |  | 75  | 70  | 67  |  | 65  |
| 6   | 84  | 74  | 68  | 63  | 83  | 73  | 67  | 63  | 72  | 66  | 62  |  | 70  | 66  | 62  |  | 60  |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 63  | 58  | 67  | 62  | 58  |  | 66  | 61  | 57  |  | 56  |
| 8   | 76  | 65  | 59  | 54  | 74  | 65  | 58  | 54  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 52  |
| 9   | 72  | 61  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 54  | 50  |  | 59  | 54  | 50  |  | 49  |
| 10  | 68  | 58  | 52  | 47  | 67  | 57  | 51  | 47  | 57  | 51  | 47  |  | 56  | 51  | 47  |  | 46  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 89795 |
| 5°  | 87365 |
| 10° | 79825 |
| 15° | 69921 |
| 20° | 59995 |
| 25° | 50084 |
| 30° | 40082 |
| 35° | 30062 |
| 40° | 21812 |
| 45° | 14265 |
| 50° | 8938  |
| 55° | 6040  |
| 60° | 5350  |
| 65° | 4929  |
| 70° | 4616  |
| 75° | 4236  |
| 80° | 4041  |
| 85° | 3522  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14265 cd/sqm

TEST NUMBER: P1253742

CATALOG NUMBER: P3AS05R109035DE010 E3DLD1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 36.6   | 10.3      |
| 10°-20°   | 85.8   | 24.1      |
| 20°-30°   | 94.6   | 26.6      |
| 30°-40°   | 70.8   | 19.9      |
| 40°-50°   | 36.7   | 10.3      |
| 50°-60°   | 15.2   | 4.3       |
| 60°-70°   | 9.4    | 2.6       |
| 70°-80°   | 5.3    | 1.5       |
| 80°-90°   | 1.6    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 217.0  | 60.9      |
| 0°-40°    | 287.8  | 80.8      |
| 0°-60°    | 339.8  | 95.4      |
| 0°-90°    | 356.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 356.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 410 |      |
| 5°  | 397 | 37   |
| 15° | 308 | 86   |
| 25° | 207 | 95   |
| 35° | 112 | 71   |
| 45° | 46  | 37   |
| 55° | 16  | 15   |
| 65° | 10  | 9    |
| 75° | 5   | 5    |
| 85° | 1   | 2    |
| 90° | 0   |      |

TEST NUMBER: P1253742

CATALOG NUMBER: P3AS05R109035DE010 E3DLD1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 409.5 |
| 1°    | 410.0 |
| 2°    | 408.6 |
| 3°    | 405.9 |
| 4°    | 401.8 |
| 5°    | 396.9 |
| 6°    | 390.6 |
| 7°    | 383.8 |
| 8°    | 375.7 |
| 9°    | 367.1 |
| 10°   | 358.5 |
| 12.5° | 333.7 |
| 15°   | 308.0 |
| 17.5° | 282.3 |
| 20°   | 257.1 |
| 22.5° | 231.4 |
| 25°   | 207.0 |
| 27.5° | 182.7 |
| 30°   | 158.3 |
| 32.5° | 134.4 |
| 35°   | 112.3 |
| 37.5° | 93.4  |
| 40°   | 76.2  |
| 42.5° | 60.4  |
| 45°   | 46.0  |
| 47.5° | 34.7  |
| 50°   | 26.2  |
| 52.5° | 19.4  |
| 55°   | 15.8  |
| 57.5° | 14.0  |
| 60°   | 12.2  |
| 62.5° | 10.8  |
| 65°   | 9.5   |
| 67.5° | 8.1   |
| 70°   | 7.2   |
| 72.5° | 5.9   |
| 75°   | 5.0   |
| 77.5° | 4.1   |
| 80°   | 3.2   |
| 82.5° | 2.3   |
| 85°   | 1.4   |
| 87.5° | 0.5   |
| 90°   | 0.0   |

(END OF REPORT)