

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254758

Luminaire Tested: P3AS13R459035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 425.0 lumens
Efficiency: N/A
Efficacy: 29.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254758

CATALOG NUMBER: P3AS13R459035DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254758

CATALOG NUMBER: P3AS13R459035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90102
5°	88510
10°	83766
15°	76391
20°	67556
25°	58649
30°	50362
35°	41947
40°	31259
45°	19134
50°	8870
55°	6920
60°	6666
65°	6123
70°	5642
75°	5422
80°	4925
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19134 cd/sqm

TEST NUMBER: P1254758

CATALOG NUMBER: P3AS13R459035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.6	8.8
10°-20°	93.7	22.0
20°-30°	111.3	26.2
30°-40°	96.7	22.8
40°-50°	48.5	11.4
50°-60°	16.9	4.0
60°-70°	11.8	2.8
70°-80°	6.6	1.5
80°-90°	2.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.6	57.1
0°-40°	339.3	79.8
0°-60°	404.6	95.2
0°-90°	425.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	425.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	411	
5°	402	38
15°	336	94
25°	242	111
35°	157	97
45°	62	49
55°	18	17
65°	12	12
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1254758

CATALOG NUMBER: P3AS13R459035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	410.9
2.5°	409.0
5°	402.1
7.5°	391.3
10°	376.2
12.5°	357.5
15°	336.5
17.5°	313.0
20°	289.5
22.5°	265.5
25°	242.4
27.5°	220.4
30°	198.9
32.5°	178.3
35°	156.7
37.5°	133.7
40°	109.2
42.5°	85.2
45°	61.7
47.5°	40.7
50°	26.0
52.5°	20.1
55°	18.1
57.5°	16.7
60°	15.2
62.5°	13.7
65°	11.8
67.5°	10.3
70°	8.8
72.5°	7.3
75°	6.4
77.5°	4.9
80°	3.9
82.5°	2.9
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)