

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253775

Luminaire Tested: P3AS05R129035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R129035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 396.0 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253775

CATALOG NUMBER: P3AS05R129035DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253775

CATALOG NUMBER: P3AS05R129035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	70	63	58	78	69	63	58	67	62	58		66	61	58		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99882
5°	97182
10°	88798
15°	77776
20°	66739
25°	55721
30°	44589
35°	33435
40°	24274
45°	15878
50°	9927
55°	6729
60°	5921
65°	5448
70°	5129
75°	4660
80°	4420
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15878 cd/sqm

TEST NUMBER: P1253775

CATALOG NUMBER: P3AS05R129035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.7	10.3
10°-20°	95.5	24.1
20°-30°	105.2	26.6
30°-40°	78.8	19.9
40°-50°	40.8	10.3
50°-60°	16.9	4.3
60°-70°	10.4	2.6
70°-80°	5.9	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.4	61.0
0°-40°	320.2	80.9
0°-60°	377.9	95.4
0°-90°	396.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	396.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	456	
5°	442	41
15°	343	95
25°	230	105
35°	125	79
45°	51	41
55°	18	17
65°	10	10
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1253775

CATALOG NUMBER: P3AS05R129035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	455.5
1°	456.0
2°	454.5
3°	451.5
4°	447.0
5°	441.5
6°	434.4
7°	426.9
8°	417.9
9°	408.4
10°	398.8
12.5°	371.2
15°	342.6
17.5°	314.0
20°	286.0
22.5°	257.4
25°	230.3
27.5°	203.2
30°	176.1
32.5°	149.5
35°	124.9
37.5°	103.8
40°	84.8
42.5°	67.2
45°	51.2
47.5°	38.6
50°	29.1
52.5°	21.6
55°	17.6
57.5°	15.6
60°	13.5
62.5°	12.0
65°	10.5
67.5°	9.0
70°	8.0
72.5°	6.5
75°	5.5
77.5°	4.5
80°	3.5
82.5°	2.5
85°	1.5
87.5°	0.5
90°	0.0

(END OF REPORT)