

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254813

Luminaire Tested: P3AS13R559035DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254813
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559035DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1090.0 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254813

CATALOG NUMBER: P3AS13R559035DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1254813

CATALOG NUMBER: P3AS13R559035DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299296
5°	296257
10°	286100
15°	264474
20°	228220
25°	180252
30°	127868
35°	82449
40°	49521
45°	27910
50°	15010
55°	5352
60°	4824
65°	4670
70°	4488
75°	4236
80°	3788
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27910 cd/sqm

TEST NUMBER: P1254813

CATALOG NUMBER: P3AS13R559035DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	11.6
10°-20°	322.1	29.6
20°-30°	337.6	31.0
30°-40°	197.0	18.1
40°-50°	73.7	6.8
50°-60°	17.3	1.6
60°-70°	8.9	0.8
70°-80°	5.3	0.5
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	786.3	72.1
0°-40°	983.3	90.2
0°-60°	1074.3	98.6
0°-90°	1090.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1090.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1365	
5°	1346	127
15°	1165	322
25°	745	338
35°	308	197
45°	90	74
55°	14	17
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1254813

CATALOG NUMBER: P3AS13R559035DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1364.9
2.5°	1360.9
5°	1345.9
7.5°	1321.9
10°	1284.9
12.5°	1232.9
15°	1165.0
17.5°	1079.0
20°	978.0
22.5°	865.0
25°	745.0
27.5°	622.0
30°	505.0
32.5°	399.0
35°	308.0
37.5°	234.0
40°	173.0
42.5°	124.0
45°	90.0
47.5°	65.0
50°	44.0
52.5°	25.0
55°	14.0
57.5°	12.0
60°	11.0
62.5°	10.0
65°	9.0
67.5°	8.0
70°	7.0
72.5°	6.0
75°	5.0
77.5°	4.0
80°	3.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)