

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254827

Luminaire Tested: P3AS13R559035DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559035DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 728.0 lumens
Efficiency: N/A
Efficacy: 49.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254827

CATALOG NUMBER: P3AS13R559035DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1254827

CATALOG NUMBER: P3AS13R559035DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	198032
5°	193066
10°	179489
15°	159842
20°	135835
25°	109627
30°	83557
35°	59428
40°	39216
45°	23258
50°	13646
55°	8411
60°	7456
65°	6745
70°	5770
75°	5083
80°	5051
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23258 cd/sqm

TEST NUMBER: P1254827

CATALOG NUMBER: P3AS13R559035DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	11.2
10°-20°	195.2	26.8
20°-30°	206.8	28.4
30°-40°	139.7	19.2
40°-50°	61.2	8.4
50°-60°	21.9	3.0
60°-70°	12.9	1.8
70°-80°	6.7	0.9
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	483.4	66.4
0°-40°	623.1	85.6
0°-60°	706.2	97.0
0°-90°	728.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	728.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	903	
5°	877	81
15°	704	195
25°	453	207
35°	222	140
45°	75	61
55°	22	22
65°	13	13
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1254827

CATALOG NUMBER: P3AS13R559035DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	903.1
2.5°	896.1
5°	877.1
7.5°	846.1
10°	806.1
12.5°	758.1
15°	704.1
17.5°	644.1
20°	582.1
22.5°	517.1
25°	453.1
27.5°	390.1
30°	330.0
32.5°	273.0
35°	222.0
37.5°	176.0
40°	137.0
42.5°	103.0
45°	75.0
47.5°	55.0
50°	40.0
52.5°	28.0
55°	22.0
57.5°	20.0
60°	17.0
62.5°	15.0
65°	13.0
67.5°	11.0
70°	9.0
72.5°	8.0
75°	6.0
77.5°	5.0
80°	4.0
82.5°	3.0
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)