

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254851

Luminaire Tested: P3AS13R609035DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254851
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609035DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 356.0 lumens
Efficiency: N/A
Efficacy: 24.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254851

CATALOG NUMBER: P3AS13R609035DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254851

CATALOG NUMBER: P3AS13R609035DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90212
5°	88201
10°	82564
15°	74075
20°	63706
25°	52672
30°	41627
35°	30918
40°	21297
45°	13366
50°	7335
55°	4320
60°	3859
65°	3321
70°	2821
75°	2881
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13366 cd/sqm

TEST NUMBER: P1254851

CATALOG NUMBER: P3AS13R609035DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.3	10.5
10°-20°	90.6	25.5
20°-30°	99.4	27.9
30°-40°	72.4	20.3
40°-50°	34.2	9.6
50°-60°	11.2	3.2
60°-70°	6.4	1.8
70°-80°	3.4	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	227.3	63.9
0°-40°	299.8	84.2
0°-60°	345.2	97.0
0°-90°	356.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	356.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	411	
5°	401	37
15°	326	91
25°	218	99
35°	116	72
45°	43	34
55°	11	11
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1254851

CATALOG NUMBER: P3AS13R609035DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	411.4
2.5°	409.0
5°	400.7
7.5°	388.0
10°	370.8
12.5°	350.3
15°	326.3
17.5°	300.4
20°	273.0
22.5°	245.1
25°	217.7
27.5°	190.3
30°	164.4
32.5°	139.4
35°	115.5
37.5°	93.9
40°	74.4
42.5°	57.2
45°	43.1
47.5°	31.3
50°	21.5
52.5°	14.2
55°	11.3
57.5°	9.8
60°	8.8
62.5°	7.3
65°	6.4
67.5°	5.4
70°	4.4
72.5°	3.9
75°	3.4
77.5°	2.4
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)