

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253851

Luminaire Tested: P3AS05R259035DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253851
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259035DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 696.0 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253851
CATALOG NUMBER: P3AS05R259035DE010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1253851

CATALOG NUMBER: P3AS05R259035DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	94	92	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	92	90	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	90	88	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	88	86	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	86	84	81
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	84	82	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	83	80	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	762242
5°	706117
10°	546327
15°	260955
20°	86037
25°	36268
30°	14053
35°	6077
40°	2032
45°	930
50°	341
55°	191
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 930 cd/sqm



TEST NUMBER: P1253851
 CATALOG NUMBER: P3AS05R259035DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.0	40.5
10°-20°	320.7	46.1
20°-30°	74.5	10.7
30°-40°	15.6	2.2
40°-50°	2.5	0.4
50°-60°	0.4	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.2	97.3
0°-40°	692.8	99.5
0°-60°	695.8	100.0
0°-90°	696.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	696.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3476	
5°	3208	282
15°	1150	321
25°	150	75
35°	23	16
45°	3	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1253851
CATALOG NUMBER: P3AS05R259035DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3476.1
1°	3469.1
2°	3433.0
3°	3382.3
4°	3304.8
5°	3207.9
6°	3083.5
7°	2953.3
8°	2807.2
9°	2642.4
10°	2453.6
11°	2234.8
12°	1983.7
13°	1708.7
14°	1421.0
15°	1149.5
16°	909.2
17°	708.3
18°	557.2
19°	445.7
20°	368.7
21°	308.1
22°	258.7
23°	216.0
24°	180.7
25°	149.9
27.5°	88.8
30°	55.5
32.5°	35.6
35°	22.7
37.5°	13.6
40°	7.1
42.5°	4.5
45°	3.0
47.5°	1.8
50°	1.0
52.5°	0.5
55°	0.5
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0



TEST NUMBER: P1253851
CATALOG NUMBER: P3AS05R259035DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)