

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254865

Luminaire Tested: P3AS13R659035DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659035DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1237.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254865
CATALOG NUMBER: P3AS13R659035DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1254865
 CATALOG NUMBER: P3AS13R659035DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75	75	75	75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70	70	70	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302300
5°	284503
10°	280890
15°	275938
20°	260539
25°	241804
30°	187953
35°	108737
40°	43825
45°	20157
50°	7846
55°	3058
60°	2631
65°	2594
70°	2565
75°	2542
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20157 cd/sqm



TEST NUMBER: P1254865
 CATALOG NUMBER: P3AS13R659035DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.9	9.9
10°-20°	339.4	27.4
20°-30°	444.3	35.9
30°-40°	257.4	20.8
40°-50°	55.1	4.5
50°-60°	9.0	0.7
60°-70°	4.9	0.4
70°-80°	2.9	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	906.6	73.3
0°-40°	1164.0	94.1
0°-60°	1228.0	99.3
0°-90°	1237.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1237.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1379	
5°	1292	123
15°	1216	339
25°	999	444
35°	406	257
45°	65	55
55°	8	9
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1254865
CATALOG NUMBER: P3AS13R659035DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1378.6
2.5°	1339.6
5°	1292.5
7.5°	1273.5
10°	1261.5
12.5°	1244.5
15°	1215.5
17.5°	1170.5
20°	1116.5
22.5°	1065.4
25°	999.4
27.5°	888.4
30°	742.3
32.5°	575.2
35°	406.2
37.5°	257.1
40°	153.1
42.5°	96.0
45°	65.0
47.5°	42.0
50°	23.0
52.5°	11.0
55°	8.0
57.5°	7.0
60°	6.0
62.5°	6.0
65°	5.0
67.5°	4.0
70°	4.0
72.5°	3.0
75°	3.0
77.5°	2.0
80°	2.0
82.5°	1.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)