

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254868

Luminaire Tested: P3AS13R659035DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659035DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 492.0 lumens
Efficiency: N/A
Efficacy: 33.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254868

CATALOG NUMBER: P3AS13R659035DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254868

CATALOG NUMBER: P3AS13R659035DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116021
5°	114638
10°	110285
15°	103315
20°	92921
25°	78900
30°	61706
35°	43982
40°	28768
45°	17800
50°	9040
55°	3173
60°	2807
65°	2802
70°	2500
75°	2457
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17800 cd/sqm

TEST NUMBER: P1254868

CATALOG NUMBER: P3AS13R659035DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.9	9.9
10°-20°	126.7	25.7
20°-30°	148.0	30.1
30°-40°	103.4	21.0
40°-50°	45.5	9.3
50°-60°	10.1	2.1
60°-70°	5.2	1.0
70°-80°	3.1	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	323.6	65.8
0°-40°	427.0	86.8
0°-60°	482.7	98.1
0°-90°	492.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	492.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	529	
5°	521	49
15°	455	127
25°	326	148
35°	164	103
45°	57	46
55°	8	10
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1254868

CATALOG NUMBER: P3AS13R659035DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	529.1
2.5°	527.2
5°	520.8
7.5°	510.0
10°	495.3
12.5°	477.1
15°	455.1
17.5°	428.1
20°	398.2
22.5°	364.4
25°	326.1
27.5°	285.9
30°	243.7
32.5°	203.0
35°	164.3
37.5°	130.4
40°	100.5
42.5°	76.0
45°	57.4
47.5°	42.2
50°	26.5
52.5°	13.7
55°	8.3
57.5°	7.4
60°	6.4
62.5°	5.9
65°	5.4
67.5°	4.4
70°	3.9
72.5°	3.4
75°	2.9
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)