

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254899

Luminaire Tested: P3AS13R709035DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709035DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1007.0 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254899
CATALOG NUMBER: P3AS13R709035DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1254899
 CATALOG NUMBER: P3AS13R709035DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194941
5°	192604
10°	187037
15°	179116
20°	167781
25°	152428
30°	131666
35°	104935
40°	76429
45°	50238
50°	23539
55°	7264
60°	7017
65°	6745
70°	6411
75°	6778
80°	6314
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 50238 cd/sqm



TEST NUMBER: P1254899
 CATALOG NUMBER: P3AS13R709035DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.4	8.2
10°-20°	220.8	21.9
20°-30°	287.0	28.5
30°-40°	243.5	24.2
40°-50°	125.6	12.5
50°-60°	24.2	2.4
60°-70°	13.1	1.3
70°-80°	8.0	0.8
80°-90°	2.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	590.2	58.6
0°-40°	833.7	82.8
0°-60°	983.5	97.7
0°-90°	1007.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1007.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	889	
5°	875	82
15°	789	221
25°	630	287
35°	392	244
45°	162	126
55°	19	24
65°	13	13
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1254899
CATALOG NUMBER: P3AS13R709035DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	889
2.5°	886
5°	875
7.5°	859
10°	840
12.5°	816
15°	789
17.5°	756
20°	719
22.5°	677
25°	630
27.5°	577
30°	520
32.5°	457
35°	392
37.5°	328
40°	267
42.5°	210
45°	162
47.5°	119
50°	69
52.5°	30
55°	19
57.5°	18
60°	16
62.5°	15
65°	13
67.5°	12
70°	10
72.5°	9
75°	8
77.5°	6
80°	5
82.5°	3
85°	2
87.5°	1
90°	0

(END OF REPORT)