

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254903

Luminaire Tested: P3AS13R709035DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254903
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709035DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 352.0 lumens
Efficiency: N/A
Efficacy: 24.1 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254903
CATALOG NUMBER: P3AS13R709035DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1254903
 CATALOG NUMBER: P3AS13R709035DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82559
5°	81048
10°	76418
15°	69353
20°	60672
25°	51172
30°	41905
35°	32498
40°	23272
45°	14730
50°	7335
55°	4511
60°	3859
65°	3580
70°	3142
75°	2881
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14730 cd/sqm



TEST NUMBER: P1254903
 CATALOG NUMBER: P3AS13R709035DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.4	9.8
10°-20°	85.0	24.1
20°-30°	96.8	27.5
30°-40°	75.7	21.5
40°-50°	37.2	10.6
50°-60°	11.4	3.3
60°-70°	6.8	1.9
70°-80°	3.6	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	216.2	61.4
0°-40°	291.9	82.9
0°-60°	340.6	96.7
0°-90°	352.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	352.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	376	
5°	368	34
15°	306	85
25°	212	97
35°	121	76
45°	48	37
55°	12	11
65°	7	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1254903
CATALOG NUMBER: P3AS13R709035DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	376.5
2.5°	374.6
5°	368.2
7.5°	357.9
10°	343.2
12.5°	326.1
15°	305.5
17.5°	283.5
20°	260.0
22.5°	235.5
25°	211.5
27.5°	188.0
30°	165.5
32.5°	143.0
35°	121.4
37.5°	100.9
40°	81.3
42.5°	63.2
45°	47.5
47.5°	33.3
50°	21.5
52.5°	14.2
55°	11.8
57.5°	10.3
60°	8.8
62.5°	7.8
65°	6.9
67.5°	5.9
70°	4.9
72.5°	3.9
75°	3.4
77.5°	2.9
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)