

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254907

Luminaire Tested: P3AS13R709035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1007.0 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254907

CATALOG NUMBER: P3AS13R709035DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1254907

CATALOG NUMBER: P3AS13R709035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	93		104	99	95	92		96	92	90		93	90	88		90	88	86
3	100	93	88	83		98	92	87	82		89	85	81		86	83	80		84	81	79
4	94	86	80	75		93	85	79	75		83	78	74		81	76	73		79	75	72
5	89	80	73	69		87	79	73	68		77	72	68		75	71	67		74	70	66
6	84	74	68	63		82	73	67	63		72	66	62		70	65	62		69	65	61
7	79	69	62	58		78	68	62	58		67	61	57		66	61	57		65	60	57
8	75	65	58	53		74	64	58	53		63	57	53		62	57	53		61	56	53
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49
10	67	57	50	46		66	56	50	46		55	50	46		55	49	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194941
5°	192604
10°	187037
15°	179116
20°	167781
25°	152428
30°	131666
35°	104935
40°	76429
45°	50238
50°	23539
55°	7264
60°	7017
65°	6745
70°	6411
75°	6778
80°	6314
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 50238 cd/sqm

TEST NUMBER: P1254907

CATALOG NUMBER: P3AS13R709035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.4	8.2
10°-20°	220.8	21.9
20°-30°	287.0	28.5
30°-40°	243.5	24.2
40°-50°	125.6	12.5
50°-60°	24.2	2.4
60°-70°	13.1	1.3
70°-80°	8.0	0.8
80°-90°	2.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	590.2	58.6
0°-40°	833.7	82.8
0°-60°	983.5	97.7
0°-90°	1007.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1007.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	889	
5°	875	82
15°	789	221
25°	630	287
35°	392	244
45°	162	126
55°	19	24
65°	13	13
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1254907

CATALOG NUMBER: P3AS13R709035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	889
2.5°	886
5°	875
7.5°	859
10°	840
12.5°	816
15°	789
17.5°	756
20°	719
22.5°	677
25°	630
27.5°	577
30°	520
32.5°	457
35°	392
37.5°	328
40°	267
42.5°	210
45°	162
47.5°	119
50°	69
52.5°	30
55°	19
57.5°	18
60°	16
62.5°	15
65°	13
67.5°	12
70°	10
72.5°	9
75°	8
77.5°	6
80°	5
82.5°	3
85°	2
87.5°	1
90°	0

(END OF REPORT)