

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253919

Luminaire Tested: P3AS05R359035DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359035DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 417.0 lumens
Efficiency: N/A
Efficacy: 57.9 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253919
CATALOG NUMBER: P3AS05R359035DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1253919
 CATALOG NUMBER: P3AS05R359035DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95256
5°	93242
10°	87306
15°	78389
20°	68186
25°	58092
30°	48666
35°	38762
40°	28024
45°	17738
50°	9654
55°	6690
60°	6315
65°	5863
70°	5642
75°	4829
80°	4546
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17738 cd/sqm



TEST NUMBER: P1253919
 CATALOG NUMBER: P3AS05R359035DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	9.5
10°-20°	96.1	23.0
20°-30°	110.1	26.4
30°-40°	89.8	21.5
40°-50°	45.3	10.9
50°-60°	16.8	4.0
60°-70°	11.3	2.7
70°-80°	6.2	1.5
80°-90°	1.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.6	58.9
0°-40°	335.4	80.4
0°-60°	397.6	95.3
0°-90°	417.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	417.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	434	
5°	424	39
15°	345	96
25°	240	110
35°	145	90
45°	57	45
55°	18	17
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1253919
CATALOG NUMBER: P3AS05R359035DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	434.4
1°	433.9
2°	432.9
3°	430.8
4°	427.7
5°	423.6
6°	418.4
7°	413.3
8°	406.6
9°	399.9
10°	392.1
11°	383.9
12°	375.1
13°	365.3
14°	355.0
15°	345.3
17.5°	319.0
20°	292.2
22.5°	264.9
25°	240.1
27.5°	215.9
30°	192.2
32.5°	168.5
35°	144.8
37.5°	121.1
40°	97.9
42.5°	76.3
45°	57.2
47.5°	41.2
50°	28.3
52.5°	20.6
55°	17.5
57.5°	16.0
60°	14.4
62.5°	12.9
65°	11.3
67.5°	9.8
70°	8.8
72.5°	7.2
75°	5.7
77.5°	4.6
80°	3.6
82.5°	2.6
85°	1.5
87.5°	1.0



TEST NUMBER: P1253919
CATALOG NUMBER: P3AS05R359035DE010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)