

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254950

Luminaire Tested: P3AS17R159035DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159035DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1676.1 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254950
CATALOG NUMBER: P3AS17R159035DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1254950
 CATALOG NUMBER: P3AS17R159035DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94	94	94
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	91	91	91
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	89	89	89
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	88	88	88
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	86	86	86
9	97	92	89	87	97	92	89	86	91	88	86	90	88	86	90	87	86	85	85	85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	84	84	84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3257743
5°	2730303
10°	1286082
15°	387743
20°	143466
25°	55794
30°	20813
35°	6398
40°	2290
45°	1240
50°	921
55°	1032
60°	1184
65°	675
70°	833
75°	1101
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1240 cd/sqm



TEST NUMBER: P1254950
 CATALOG NUMBER: P3AS17R159035DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	958.9	57.2
10°-20°	570.0	34.0
20°-30°	119.7	7.1
30°-40°	19.3	1.2
40°-50°	3.3	0.2
50°-60°	2.4	0.1
60°-70°	1.5	0.1
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1648.7	98.4
0°-40°	1668.0	99.5
0°-60°	1673.8	99.9
0°-90°	1676.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1676.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14856	
5°	12404	959
15°	1708	570
25°	231	120
35°	24	19
45°	4	3
55°	3	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1254950
CATALOG NUMBER: P3AS17R159035DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	14856.5
1°	14810.1
2°	14574.3
3°	14102.5
4°	13410.9
5°	12403.8
6°	11220.6
7°	9867.7
8°	8575.7
9°	7112.9
10°	5775.9
12.5°	3116.5
15°	1708.0
17.5°	1000.4
20°	614.8
22.5°	376.3
25°	230.6
27.5°	139.1
30°	82.2
32.5°	46.4
35°	23.9
37.5°	13.3
40°	8.0
42.5°	5.3
45°	4.0
47.5°	2.7
50°	2.7
52.5°	2.7
55°	2.7
57.5°	2.7
60°	2.7
62.5°	1.3
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)