

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253970

Luminaire Tested: P3AS05R459035DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459035DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 576.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253970
CATALOG NUMBER: P3AS05R459035DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1253970
 CATALOG NUMBER: P3AS05R459035DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74			74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70			70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62			62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59			59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216298
5°	211248
10°	194185
15°	164541
20°	127668
25°	89231
30°	56211
35°	33087
40°	18721
45°	9117
50°	3173
55°	2561
60°	2500
65°	2387
70°	2308
75°	2203
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9117 cd/sqm



TEST NUMBER: P1253970
 CATALOG NUMBER: P3AS05R459035DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	15.4
10°-20°	199.0	34.6
20°-30°	169.0	29.3
30°-40°	80.6	14.0
40°-50°	24.3	4.2
50°-60°	6.2	1.1
60°-70°	4.6	0.8
70°-80°	2.7	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.9	79.3
0°-40°	537.5	93.3
0°-60°	567.9	98.6
0°-90°	576.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	576.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	986	
5°	960	89
15°	725	199
25°	369	169
35°	124	81
45°	29	24
55°	7	6
65°	5	5
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1253970
CATALOG NUMBER: P3AS05R459035DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	986.4
2.5°	980.3
5°	959.7
7.5°	924.1
10°	872.1
12.5°	803.1
15°	724.8
17.5°	637.7
20°	547.1
22.5°	454.8
25°	368.8
27.5°	290.5
30°	222.0
32.5°	166.9
35°	123.6
37.5°	91.2
40°	65.4
42.5°	45.3
45°	29.4
47.5°	16.5
50°	9.3
52.5°	7.2
55°	6.7
57.5°	6.2
60°	5.7
62.5°	5.2
65°	4.6
67.5°	4.1
70°	3.6
72.5°	3.1
75°	2.6
77.5°	2.1
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)