

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253985

Luminaire Tested: P3AS05R459035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 576.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253985

CATALOG NUMBER: P3AS05R459035DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1253985

CATALOG NUMBER: P3AS05R459035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216298
5°	211248
10°	194185
15°	164541
20°	127668
25°	89231
30°	56211
35°	33087
40°	18721
45°	9117
50°	3173
55°	2561
60°	2500
65°	2387
70°	2308
75°	2203
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9117 cd/sqm

TEST NUMBER: P1253985

CATALOG NUMBER: P3AS05R459035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	15.4
10°-20°	199.0	34.6
20°-30°	169.0	29.3
30°-40°	80.6	14.0
40°-50°	24.3	4.2
50°-60°	6.2	1.1
60°-70°	4.6	0.8
70°-80°	2.7	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.9	79.3
0°-40°	537.5	93.3
0°-60°	567.9	98.6
0°-90°	576.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	576.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	986	
5°	960	89
15°	725	199
25°	369	169
35°	124	81
45°	29	24
55°	7	6
65°	5	5
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1253985

CATALOG NUMBER: P3AS05R459035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	986.4
2.5°	980.3
5°	959.7
7.5°	924.1
10°	872.1
12.5°	803.1
15°	724.8
17.5°	637.7
20°	547.1
22.5°	454.8
25°	368.8
27.5°	290.5
30°	222.0
32.5°	166.9
35°	123.6
37.5°	91.2
40°	65.4
42.5°	45.3
45°	29.4
47.5°	16.5
50°	9.3
52.5°	7.2
55°	6.7
57.5°	6.2
60°	5.7
62.5°	5.2
65°	4.6
67.5°	4.1
70°	3.6
72.5°	3.1
75°	2.6
77.5°	2.1
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)