

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254975

Luminaire Tested: P3AS17R209035DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209035DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1672.9 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254975

CATALOG NUMBER: P3AS17R209035DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1254975

CATALOG NUMBER: P3AS17R209035DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98		
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	95		
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	93		
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92	91		
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	90		
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	88		
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	86		
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85		
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	83		
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	87	84	82	82		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2598366
5°	2255288
10°	1393517
15°	484021
20°	148646
25°	52551
30°	19446
35°	7790
40°	4179
45°	1644
50°	887
55°	994
60°	1140
65°	675
70°	833
75°	1101
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1644 cd/sqm

TEST NUMBER: P1254975

CATALOG NUMBER: P3AS17R209035DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	850.3	50.8
10°-20°	674.7	40.3
20°-30°	116.8	7.0
30°-40°	21.2	1.3
40°-50°	4.9	0.3
50°-60°	2.3	0.1
60°-70°	1.4	0.1
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1641.8	98.1
0°-40°	1663.1	99.4
0°-60°	1670.3	99.8
0°-90°	1672.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1672.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11850	
5°	10246	850
15°	2132	675
25°	217	117
35°	29	21
45°	5	5
55°	3	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1254975

CATALOG NUMBER: P3AS17R209035DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	11849.5
1°	11792.5
2°	11567.4
3°	11205.9
4°	10782.1
5°	10245.8
6°	9631.3
7°	8916.2
8°	8101.8
9°	7186.8
10°	6258.4
12.5°	3947.6
15°	2132.1
17.5°	1138.9
20°	637.0
22.5°	364.2
25°	217.2
27.5°	132.4
30°	76.8
32.5°	45.0
35°	29.1
37.5°	19.9
40°	14.6
42.5°	9.3
45°	5.3
47.5°	2.6
50°	2.6
52.5°	2.6
55°	2.6
57.5°	2.6
60°	2.6
62.5°	1.3
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)