

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254991

Luminaire Tested: P3AS17R209035DE010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1254991  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R209035DE010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1043.0 lumens  
Efficiency: N/A  
Efficacy: 49.2 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1254991

CATALOG NUMBER: P3AS17R209035DE010 E3DLD1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1254991

CATALOG NUMBER: P3AS17R209035DE010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 91  |    |    |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 90  | 87  | 85  | 83  |    |    |
| 3   | 100 | 93  | 87  | 82  | 98  | 91  | 86  | 82  | 88  | 84  | 80  | 86  | 82  | 79  | 84  | 81  | 78  | 76  |    |    |
| 4   | 94  | 86  | 79  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  | 80  | 76  | 72  | 78  | 75  | 72  | 70  |    |    |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 71  | 67  | 75  | 70  | 67  | 73  | 69  | 66  | 65  |    |    |
| 6   | 84  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 66  | 62  | 70  | 65  | 62  | 69  | 65  | 61  | 60  |    |    |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 62  | 58  | 67  | 62  | 58  | 66  | 61  | 57  | 65  | 60  | 57  | 55  |    |    |
| 8   | 75  | 65  | 59  | 54  | 74  | 64  | 58  | 54  | 63  | 58  | 54  | 62  | 57  | 53  | 61  | 57  | 53  | 52  |    |    |
| 9   | 72  | 61  | 55  | 50  | 70  | 61  | 55  | 50  | 60  | 54  | 50  | 59  | 54  | 50  | 58  | 53  | 50  | 48  |    |    |
| 10  | 68  | 58  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 51  | 47  | 56  | 51  | 47  | 55  | 50  | 47  | 45  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 257984 |
| 5°  | 251089 |
| 10° | 230991 |
| 15° | 203316 |
| 20° | 174362 |
| 25° | 146500 |
| 30° | 118423 |
| 35° | 90078  |
| 40° | 64092  |
| 45° | 42330  |
| 50° | 26200  |
| 55° | 17204  |
| 60° | 15700  |
| 65° | 14424  |
| 70° | 13592  |
| 75° | 12370  |
| 80° | 11744  |
| 85° | 10064  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42330 cd/sqm

TEST NUMBER: P1254991

CATALOG NUMBER: P3AS17R209035DE010 E3DLD1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 105.5  | 10.1      |
| 10°-20°   | 249.3  | 23.9      |
| 20°-30°   | 276.8  | 26.5      |
| 30°-40°   | 211.1  | 20.2      |
| 40°-50°   | 108.1  | 10.4      |
| 50°-60°   | 44.4   | 4.3       |
| 60°-70°   | 27.7   | 2.7       |
| 70°-80°   | 15.5   | 1.5       |
| 80°-90°   | 4.5    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 631.6  | 60.6      |
| 0°-40°    | 842.7  | 80.8      |
| 0°-60°    | 995.2  | 95.4      |
| 0°-90°    | 1043.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1043.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1176 |      |
| 5°  | 1141 | 106  |
| 15° | 896  | 249  |
| 25° | 606  | 277  |
| 35° | 336  | 211  |
| 45° | 136  | 108  |
| 55° | 45   | 44   |
| 65° | 28   | 28   |
| 75° | 15   | 16   |
| 85° | 4    | 5    |
| 90° | 0    |      |

TEST NUMBER: P1254991

CATALOG NUMBER: P3AS17R209035DE010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1176.5 |
| 1°    | 1177.8 |
| 2°    | 1172.5 |
| 3°    | 1165.9 |
| 4°    | 1155.3 |
| 5°    | 1140.7 |
| 6°    | 1123.5 |
| 7°    | 1105.0 |
| 8°    | 1085.1 |
| 9°    | 1061.2 |
| 10°   | 1037.4 |
| 12.5° | 968.5  |
| 15°   | 895.6  |
| 17.5° | 821.4  |
| 20°   | 747.2  |
| 22.5° | 673.1  |
| 25°   | 605.5  |
| 27.5° | 537.9  |
| 30°   | 467.7  |
| 32.5° | 401.4  |
| 35°   | 336.5  |
| 37.5° | 279.6  |
| 40°   | 223.9  |
| 42.5° | 176.2  |
| 45°   | 136.5  |
| 47.5° | 103.3  |
| 50°   | 76.8   |
| 52.5° | 57.0   |
| 55°   | 45.0   |
| 57.5° | 41.1   |
| 60°   | 35.8   |
| 62.5° | 31.8   |
| 65°   | 27.8   |
| 67.5° | 23.8   |
| 70°   | 21.2   |
| 72.5° | 17.2   |
| 75°   | 14.6   |
| 77.5° | 11.9   |
| 80°   | 9.3    |
| 82.5° | 6.6    |
| 85°   | 4.0    |
| 87.5° | 1.3    |
| 90°   | 0.0    |

(END OF REPORT)