

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254072

Luminaire Tested: P3AS05R609035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 542.0 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254072

CATALOG NUMBER: P3AS05R609035DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1254072

CATALOG NUMBER: P3AS05R609035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		59
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		51
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127994
5°	126766
10°	123066
15°	115301
20°	102069
25°	85384
30°	66922
35°	48533
40°	32289
45°	20126
50°	10882
55°	3135
60°	2938
65°	2698
70°	2629
75°	2626
80°	2652
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 20126 cd/sqm

TEST NUMBER: P1254072

CATALOG NUMBER: P3AS05R609035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	10.0
10°-20°	140.9	26.0
20°-30°	160.6	29.6
30°-40°	113.9	21.0
40°-50°	51.7	9.5
50°-60°	10.9	2.0
60°-70°	5.3	1.0
70°-80°	3.3	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.8	65.6
0°-40°	469.7	86.7
0°-60°	532.3	98.2
0°-90°	542.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	542.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	584	
5°	576	54
15°	508	141
25°	353	161
35°	181	114
45°	65	52
55°	8	11
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1254072

CATALOG NUMBER: P3AS05R609035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	583.7
2.5°	581.6
5°	575.9
7.5°	566.1
10°	552.7
12.5°	533.7
15°	507.9
17.5°	475.5
20°	437.4
22.5°	396.1
25°	352.9
27.5°	308.6
30°	264.3
32.5°	222.0
35°	181.3
37.5°	145.3
40°	112.8
42.5°	85.5
45°	64.9
47.5°	48.4
50°	31.9
52.5°	14.9
55°	8.2
57.5°	7.2
60°	6.7
62.5°	6.2
65°	5.2
67.5°	4.6
70°	4.1
72.5°	3.6
75°	3.1
77.5°	2.6
80°	2.1
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)