

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254073

Luminaire Tested: P3AS05R609035DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609035DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 375.0 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254073

CATALOG NUMBER: P3AS05R609035DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1254073

CATALOG NUMBER: P3AS05R609035DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95036
5°	92912
10°	86972
15°	78025
20°	67113
25°	55479
30°	43855
35°	32551
40°	22413
45°	14048
50°	7744
55°	4549
60°	4079
65°	3476
70°	2949
75°	3050
80°	2652
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14048 cd/sqm

TEST NUMBER: P1254073

CATALOG NUMBER: P3AS05R609035DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	10.5
10°-20°	95.5	25.5
20°-30°	104.7	27.9
30°-40°	76.3	20.3
40°-50°	36.0	9.6
50°-60°	11.8	3.1
60°-70°	6.7	1.8
70°-80°	3.6	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.5	63.9
0°-40°	315.8	84.2
0°-60°	363.6	97.0
0°-90°	375.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	375.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	433	
5°	422	39
15°	344	95
25°	229	105
35°	122	76
45°	45	36
55°	12	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1254073

CATALOG NUMBER: P3AS05R609035DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	433.4
2.5°	430.8
5°	422.1
7.5°	408.7
10°	390.6
12.5°	369.0
15°	343.7
17.5°	316.4
20°	287.6
22.5°	258.2
25°	229.3
27.5°	200.5
30°	173.2
32.5°	146.9
35°	121.6
37.5°	98.9
40°	78.3
42.5°	60.3
45°	45.3
47.5°	33.0
50°	22.7
52.5°	14.9
55°	11.9
57.5°	10.3
60°	9.3
62.5°	7.7
65°	6.7
67.5°	5.7
70°	4.6
72.5°	4.1
75°	3.6
77.5°	2.6
80°	2.1
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)