

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255016

Luminaire Tested: P3AS17R259035DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259035DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1387.0 lumens
Efficiency: N/A
Efficacy: 65.4 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255016
CATALOG NUMBER: P3AS17R259035DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1255016
 CATALOG NUMBER: P3AS17R259035DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.6	24.1
10°-20°	546.6	39.4
20°-30°	312.3	22.5
30°-40°	123.3	8.9
40°-50°	37.8	2.7
50°-60°	14.9	1.1
60°-70°	10.0	0.7
70°-80°	5.6	0.4
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1193.6	86.1
0°-40°	1316.9	94.9
0°-60°	1369.6	98.7
0°-90°	1387.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1387.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4057	
5°	3771	335
15°	1988	547
25°	660	312
35°	187	123
45°	45	38
55°	16	15
65°	11	10
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P1255016
CATALOG NUMBER: P3AS17R259035DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4057.4
1°	4049.4
2°	4016.3
3°	3958.0
4°	3877.1
5°	3771.1
6°	3646.5
7°	3506.0
8°	3342.9
9°	3175.9
10°	2986.4
11°	2799.5
12°	2594.0
13°	2391.2
14°	2183.1
15°	1988.3
17.5°	1541.6
20°	1170.4
22.5°	878.8
25°	660.1
27.5°	489.1
30°	359.2
32.5°	259.8
35°	186.9
37.5°	132.6
40°	92.8
42.5°	63.6
45°	45.1
47.5°	31.8
50°	23.9
52.5°	18.6
55°	15.9
57.5°	14.6
60°	11.9
62.5°	10.6
65°	10.6
67.5°	9.3
70°	8.0
72.5°	6.6
75°	5.3
77.5°	4.0
80°	2.7
82.5°	2.7
85°	1.3
87.5°	1.3



TEST NUMBER: P1255016
CATALOG NUMBER: P3AS17R259035DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)