

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254092

Luminaire Tested: P3AS05R659035DE010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1254092  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R659035DE010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 406.0 lumens  
Efficiency: N/A  
Efficacy: 56.4 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1254092  
CATALOG NUMBER: P3AS05R659035DE010 E3DLD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1254092  
 CATALOG NUMBER: P3AS05R659035DE010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61		
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44		
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72253
5°	71274
10°	68892
15°	64972
20°	59925
25°	54390
30°	48185
35°	40984
40°	32633
45°	23010
50°	13373
55°	7302
60°	6798
65°	6174
70°	5642
75°	5253
80°	4546
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 23010 cd/sqm



TEST NUMBER: P1254092  
 CATALOG NUMBER: P3AS05R659035DE010 E3DLD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	30.5	7.5
10°-20°	80.1	19.7
20°-30°	102.9	25.3
30°-40°	95.2	23.4
40°-50°	57.4	14.1
50°-60°	19.6	4.8
60°-70°	11.8	2.9
70°-80°	6.7	1.6
80°-90°	1.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	213.4	52.6
0°-40°	308.6	76.0
0°-60°	385.6	95.0
0°-90°	406.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	406.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	330	
5°	324	30
15°	286	80
25°	225	103
35°	153	95
45°	74	57
55°	19	20
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1254092  
CATALOG NUMBER: P3AS05R659035DE010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	329.5
2.5°	327.9
5°	323.8
7.5°	317.6
10°	309.4
12.5°	299.1
15°	286.2
17.5°	272.2
20°	256.8
22.5°	240.8
25°	224.8
27.5°	207.8
30°	190.3
32.5°	172.7
35°	153.1
37.5°	134.1
40°	114.0
42.5°	93.8
45°	74.2
47.5°	56.2
50°	39.2
52.5°	24.7
55°	19.1
57.5°	17.0
60°	15.5
62.5°	13.4
65°	11.9
67.5°	10.3
70°	8.8
72.5°	7.7
75°	6.2
77.5°	5.2
80°	3.6
82.5°	2.6
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)