

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255030

Luminaire Tested: P3AS17R259035DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255030
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259035DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1064.0 lumens
Efficiency: N/A
Efficacy: 50.2 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255030
CATALOG NUMBER: P3AS17R259035DE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1255030
 CATALOG NUMBER: P3AS17R259035DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	69	65	61	59
6	81	70	63	58	79	69	62	57	68	62	57	66	61	57	65	60	56	65	60	56	55
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	61	56	52	50
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	57	52	48	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	43	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	277609
5°	263526
10°	228252
15°	185813
20°	146826
25°	117079
30°	94901
35°	77310
40°	64063
45°	53959
50°	45679
55°	40218
60°	35216
65°	30769
70°	26992
75°	22706
80°	16921
85°	9561

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 53959 cd/sqm



TEST NUMBER: P1255030
 CATALOG NUMBER: P3AS17R259035DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.7	10.2
10°-20°	227.0	21.3
20°-30°	223.7	21.0
30°-40°	182.1	17.1
40°-50°	135.1	12.7
50°-60°	94.3	8.9
60°-70°	59.1	5.6
70°-80°	28.5	2.7
80°-90°	5.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.4	52.6
0°-40°	741.5	69.7
0°-60°	971.0	91.3
0°-90°	1064.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1064.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1266	
5°	1197	109
15°	818	227
25°	484	224
35°	289	182
45°	174	135
55°	105	94
65°	59	59
75°	27	28
85°	4	5
90°	0	



TEST NUMBER: P1255030
CATALOG NUMBER: P3AS17R259035DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1266.0
2.5°	1248.8
5°	1197.2
7.5°	1118.8
10°	1025.1
12.5°	921.8
15°	818.5
17.5°	717.2
20°	629.2
22.5°	552.7
25°	483.9
27.5°	424.6
30°	374.8
32.5°	328.9
35°	288.8
37.5°	254.4
40°	223.8
42.5°	197.0
45°	174.0
47.5°	153.0
50°	133.9
52.5°	118.6
55°	105.2
57.5°	91.8
60°	80.3
62.5°	68.8
65°	59.3
67.5°	49.7
70°	42.1
72.5°	34.4
75°	26.8
77.5°	19.1
80°	13.4
82.5°	7.6
85°	3.8
87.5°	1.9
90°	0.0

(END OF REPORT)