

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254120

Luminaire Tested: P3AS05R709035DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709035DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 182.0 lumens
Efficiency: N/A
Efficacy: 25.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254120

CATALOG NUMBER: P3AS05R709035DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254120

CATALOG NUMBER: P3AS05R709035DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42694
5°	41911
10°	39523
15°	35869
20°	31363
25°	26469
30°	21674
35°	16811
40°	12023
45°	7629
50°	3787
55°	2332
60°	2017
65°	1816
70°	1603
75°	1525
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7629 cd/sqm

TEST NUMBER: P1254120

CATALOG NUMBER: P3AS05R709035DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.8	9.8
10°-20°	44.0	24.2
20°-30°	50.1	27.5
30°-40°	39.2	21.5
40°-50°	19.2	10.6
50°-60°	5.9	3.2
60°-70°	3.5	1.9
70°-80°	1.9	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	111.8	61.4
0°-40°	150.9	82.9
0°-60°	176.1	96.7
0°-90°	182.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	182.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	195	
5°	190	18
15°	158	44
25°	109	50
35°	63	39
45°	25	19
55°	6	6
65°	4	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1254120

CATALOG NUMBER: P3AS05R709035DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	194.7
2.5°	193.7
5°	190.4
7.5°	185.1
10°	177.5
12.5°	168.6
15°	158.0
17.5°	146.6
20°	134.4
22.5°	121.8
25°	109.4
27.5°	97.2
30°	85.6
32.5°	73.9
35°	62.8
37.5°	52.2
40°	42.0
42.5°	32.7
45°	24.6
47.5°	17.2
50°	11.1
52.5°	7.3
55°	6.1
57.5°	5.3
60°	4.6
62.5°	4.1
65°	3.5
67.5°	3.0
70°	2.5
72.5°	2.0
75°	1.8
77.5°	1.5
80°	1.0
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)