

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254149

Luminaire Tested: P3AS09R109035DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R109035DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R10 optic, 3500K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 474.9 lumens
Efficiency: N/A
Efficacy: 38.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254149

CATALOG NUMBER: P3AS09R109035DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1254149

CATALOG NUMBER: P3AS09R109035DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	70	63	58	78	69	63	58	67	62	58		66	61	58		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119815
5°	116553
10°	106522
15°	93304
20°	80040
25°	66826
30°	53477
35°	40100
40°	29112
45°	19041
50°	11906
55°	8067
60°	7105
65°	6538
70°	6155
75°	5592
80°	5304
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19041 cd/sqm

TEST NUMBER: P1254149

CATALOG NUMBER: P3AS09R109035DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.9	10.3
10°-20°	114.5	24.1
20°-30°	126.2	26.6
30°-40°	94.5	19.9
40°-50°	49.0	10.3
50°-60°	20.3	4.3
60°-70°	12.5	2.6
70°-80°	7.0	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	289.6	61.0
0°-40°	384.0	80.9
0°-60°	453.3	95.4
0°-90°	474.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	474.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	546	
5°	530	49
15°	411	115
25°	276	126
35°	150	94
45°	61	49
55°	21	20
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1254149

CATALOG NUMBER: P3AS09R109035DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	546.4
1°	547.0
2°	545.2
3°	541.6
4°	536.2
5°	529.5
6°	521.1
7°	512.1
8°	501.3
9°	489.8
10°	478.4
12.5°	445.3
15°	411.0
17.5°	376.7
20°	343.0
22.5°	308.7
25°	276.2
27.5°	243.7
30°	211.2
32.5°	179.3
35°	149.8
37.5°	124.6
40°	101.7
42.5°	80.6
45°	61.4
47.5°	46.3
50°	34.9
52.5°	25.9
55°	21.1
57.5°	18.7
60°	16.2
62.5°	14.4
65°	12.6
67.5°	10.8
70°	9.6
72.5°	7.8
75°	6.6
77.5°	5.4
80°	4.2
82.5°	3.0
85°	1.8
87.5°	0.6
90°	0.0

(END OF REPORT)