

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255052

Luminaire Tested: P3AS17R309035DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309035DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1079.0 lumens
Efficiency: N/A
Efficacy: 50.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255052

CATALOG NUMBER: P3AS17R309035DE010 E3DLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1255052

CATALOG NUMBER: P3AS17R309035DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	254914
5°	249196
10°	231726
15°	206199
20°	177349
25°	150251
30°	124703
35°	97815
40°	70103
45°	45989
50°	26200
55°	17204
60°	16271
65°	15099
70°	13592
75°	12370
80°	11744
85°	10064

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 45989 cd/sqm

TEST NUMBER: P1255052

CATALOG NUMBER: P3AS17R309035DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.1	9.7
10°-20°	252.5	23.4
20°-30°	284.6	26.4
30°-40°	227.2	21.1
40°-50°	116.8	10.8
50°-60°	43.9	4.1
60°-70°	28.8	2.7
70°-80°	15.5	1.4
80°-90°	4.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	642.2	59.5
0°-40°	869.4	80.6
0°-60°	1030.1	95.5
0°-90°	1079.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1079.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1162	
5°	1132	105
15°	908	252
25°	621	285
35°	365	227
45°	148	117
55°	45	44
65°	29	29
75°	15	16
85°	4	5
90°	0	

TEST NUMBER: P1255052

CATALOG NUMBER: P3AS17R309035DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1162.5
1°	1162.5
2°	1158.5
3°	1151.9
4°	1142.6
5°	1132.1
6°	1118.8
7°	1101.6
8°	1083.1
9°	1061.9
10°	1040.7
11°	1016.9
12°	991.7
13°	965.2
14°	937.4
15°	908.3
17.5°	834.1
20°	760.0
22.5°	688.5
25°	621.0
27.5°	554.8
30°	492.5
32.5°	429.0
35°	365.4
37.5°	303.2
40°	244.9
42.5°	193.3
45°	148.3
47.5°	109.9
50°	76.8
52.5°	54.3
55°	45.0
57.5°	41.0
60°	37.1
62.5°	33.1
65°	29.1
67.5°	25.2
70°	21.2
72.5°	17.2
75°	14.6
77.5°	11.9
80°	9.3
82.5°	6.6
85°	4.0
87.5°	1.3



TEST NUMBER: P1255052
CATALOG NUMBER: P3AS17R309035DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)