

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255068

Luminaire Tested: P3AS17R359035DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359035DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1683.1 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255068
CATALOG NUMBER: P3AS17R359035DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1255068
 CATALOG NUMBER: P3AS17R359035DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93	93	93	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89	89	89	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86	86	86	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83	83	83	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	77	77	77	77
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75	75	75	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73	73	73	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70	70	70	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1097434
5°	1075080
10°	1000137
15°	733262
20°	375466
25°	135322
30°	52692
35°	18444
40°	7586
45°	2047
50°	1808
55°	2026
60°	1754
65°	1401
70°	1731
75°	2288
80°	1642
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 2288 cd/sqm



TEST NUMBER: P1255068
 CATALOG NUMBER: P3AS17R359035DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	455.3	27.1
10°-20°	854.3	50.8
20°-30°	302.5	18.0
30°-40°	53.0	3.1
40°-50°	7.8	0.5
50°-60°	4.3	0.3
60°-70°	3.2	0.2
70°-80°	2.3	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1612.1	95.8
0°-40°	1665.0	98.9
0°-60°	1677.1	99.6
0°-90°	1683.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1683.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5005	
5°	4884	455
15°	3230	854
25°	559	302
35°	69	53
45°	7	8
55°	5	4
65°	3	3
75°	3	2
85°	0	1
90°	0	



TEST NUMBER: P1255068
CATALOG NUMBER: P3AS17R359035DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	5004.7
1°	5003.3
2°	4987.4
3°	4957.0
4°	4929.1
5°	4884.1
6°	4837.7
7°	4786.0
8°	4722.4
9°	4623.0
10°	4491.7
11°	4310.2
12°	4091.5
13°	3831.7
14°	3545.4
15°	3230.0
17.5°	2405.6
20°	1609.0
22.5°	970.2
25°	559.3
27.5°	334.0
30°	208.1
32.5°	120.6
35°	68.9
37.5°	43.7
40°	26.5
42.5°	13.3
45°	6.6
47.5°	5.3
50°	5.3
52.5°	5.3
55°	5.3
57.5°	4.0
60°	4.0
62.5°	4.0
65°	2.7
67.5°	2.7
70°	2.7
72.5°	2.7
75°	2.7
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0



TEST NUMBER: P1255068
CATALOG NUMBER: P3AS17R359035DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)