

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255082

Luminaire Tested: P3AS17R359035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1072.0 lumens
Efficiency: N/A
Efficacy: 50.6 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255082
CATALOG NUMBER: P3AS17R359035DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1255082
 CATALOG NUMBER: P3AS17R359035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	244871
5°	239687
10°	224467
15°	201499
20°	175272
25°	149355
30°	125108
35°	99635
40°	72049
45°	45586
50°	24869
55°	17204
60°	16271
65°	15099
70°	14426
75°	12370
80°	11744
85°	10064

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 45586 cd/sqm



TEST NUMBER: P1255082

CATALOG NUMBER: P3AS17R359035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.3	9.5
10°-20°	247.0	23.0
20°-30°	283.1	26.4
30°-40°	231.0	21.5
40°-50°	116.5	10.9
50°-60°	43.3	4.0
60°-70°	29.0	2.7
70°-80°	16.1	1.5
80°-90°	4.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	631.4	58.9
0°-40°	862.3	80.4
0°-60°	1022.1	95.3
0°-90°	1072.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1072.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1117	
5°	1089	101
15°	888	247
25°	617	283
35°	372	231
45°	147	116
55°	45	43
65°	29	29
75°	15	16
85°	4	5
90°	0	



TEST NUMBER: P1255082

CATALOG NUMBER: P3AS17R359035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1116.7
1°	1115.4
2°	1112.8
3°	1107.5
4°	1099.5
5°	1088.9
6°	1075.7
7°	1062.4
8°	1045.2
9°	1028.0
10°	1008.1
11°	986.9
12°	964.4
13°	939.2
14°	912.7
15°	887.6
17.5°	820.0
20°	751.1
22.5°	680.9
25°	617.3
27.5°	555.1
30°	494.1
32.5°	433.2
35°	372.2
37.5°	311.3
40°	251.7
42.5°	196.1
45°	147.0
47.5°	106.0
50°	72.9
52.5°	53.0
55°	45.0
57.5°	41.1
60°	37.1
62.5°	33.1
65°	29.1
67.5°	25.2
70°	22.5
72.5°	18.5
75°	14.6
77.5°	11.9
80°	9.3
82.5°	6.6
85°	4.0
87.5°	2.6



TEST NUMBER: P1255082
CATALOG NUMBER: P3AS17R359035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)