

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254238

Luminaire Tested: P3AS09R259035DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254238
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259035DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 604.1 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254238

CATALOG NUMBER: P3AS09R259035DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1254238

CATALOG NUMBER: P3AS09R259035DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143541
5°	140127
10°	129857
15°	115642
20°	99385
25°	84465
30°	69530
35°	54181
40°	38987
45°	24747
50°	14635
55°	10055
60°	9254
65°	8613
70°	7694
75°	7032
80°	6693
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24747 cd/sqm

TEST NUMBER: P1254238

CATALOG NUMBER: P3AS09R259035DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.0	9.8
10°-20°	141.4	23.4
20°-30°	159.8	26.5
30°-40°	126.4	20.9
40°-50°	63.8	10.6
50°-60°	25.6	4.2
60°-70°	16.4	2.7
70°-80°	9.0	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.2	59.6
0°-40°	486.6	80.6
0°-60°	576.1	95.4
0°-90°	604.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	604.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	655	
5°	637	59
15°	509	141
25°	349	160
35°	202	126
45°	80	64
55°	26	26
65°	17	16
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1254238

CATALOG NUMBER: P3AS09R259035DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	654.6
1°	654.6
2°	652.4
3°	648.6
4°	643.4
5°	636.6
6°	628.3
7°	618.5
8°	608.0
9°	595.9
10°	583.2
11°	568.9
12°	555.3
13°	539.5
14°	524.5
15°	509.4
17.5°	467.3
20°	425.9
22.5°	386.8
25°	349.1
27.5°	312.3
30°	274.6
32.5°	239.3
35°	202.4
37.5°	168.6
40°	136.2
42.5°	106.1
45°	79.8
47.5°	59.4
50°	42.9
52.5°	32.4
55°	26.3
57.5°	24.1
60°	21.1
62.5°	18.8
65°	16.6
67.5°	14.3
70°	12.0
72.5°	10.5
75°	8.3
77.5°	6.8
80°	5.3
82.5°	3.8
85°	2.3
87.5°	0.8

TEST NUMBER: P1254238

CATALOG NUMBER: P3AS09R259035DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)