

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254244

Luminaire Tested: P3AS09R259035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254244
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 788.0 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254244
CATALOG NUMBER: P3AS09R259035DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1254244

CATALOG NUMBER: P3AS09R259035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	92	92	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	87	87	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	83	83	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	79	79	79	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	76	76	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	73	73	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	67	67	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	65	65	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	505464
5°	471603
10°	377793
15°	256437
20°	155180
25°	90731
30°	51679
35°	28429
40°	15085
45°	7939
50°	4640
55°	3441
60°	2982
65°	3113
70°	2885
75°	2542
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7939 cd/sqm



TEST NUMBER: P1254244
 CATALOG NUMBER: P3AS09R259035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.1	24.1
10°-20°	310.6	39.4
20°-30°	177.5	22.5
30°-40°	70.0	8.9
40°-50°	21.5	2.7
50°-60°	8.5	1.1
60°-70°	5.7	0.7
70°-80°	3.2	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	678.1	86.1
0°-40°	748.2	94.9
0°-60°	778.1	98.7
0°-90°	788.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	788.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2305	
5°	2142	190
15°	1130	311
25°	375	177
35°	106	70
45°	26	21
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1254244

CATALOG NUMBER: P3AS09R259035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2305.1
1°	2300.6
2°	2281.8
3°	2248.7
4°	2202.7
5°	2142.5
6°	2071.7
7°	1991.9
8°	1899.2
9°	1804.3
10°	1696.7
11°	1590.5
12°	1473.8
13°	1358.5
14°	1240.3
15°	1129.6
17.5°	875.8
20°	665.0
22.5°	499.3
25°	375.0
27.5°	277.9
30°	204.1
32.5°	147.6
35°	106.2
37.5°	75.3
40°	52.7
42.5°	36.1
45°	25.6
47.5°	18.1
50°	13.6
52.5°	10.5
55°	9.0
57.5°	8.3
60°	6.8
62.5°	6.0
65°	6.0
67.5°	5.3
70°	4.5
72.5°	3.8
75°	3.0
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.8



TEST NUMBER: P1254244
CATALOG NUMBER: P3AS09R259035DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)