

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254277

Luminaire Tested: P3AS09R309035DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309035DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 486.1 lumens
Efficiency: N/A
Efficacy: 43.8 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254277

CATALOG NUMBER: P3AS09R309035DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1254277

CATALOG NUMBER: P3AS09R309035DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		86
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		80
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		74
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		65
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		61
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		58
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		55
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166083
5°	160906
10°	144976
15°	119933
20°	92851
25°	69657
30°	50565
35°	33702
40°	20696
45°	12156
50°	7471
55°	6040
60°	5307
65°	4307
70°	3847
75°	3813
80°	2904
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12156 cd/sqm

TEST NUMBER: P1254277

CATALOG NUMBER: P3AS09R309035DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.2	13.8
10°-20°	145.5	29.9
20°-30°	132.4	27.2
30°-40°	80.0	16.5
40°-50°	32.1	6.6
50°-60°	14.2	2.9
60°-70°	8.6	1.8
70°-80°	4.7	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	345.1	71.0
0°-40°	425.2	87.5
0°-60°	471.5	97.0
0°-90°	486.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	486.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	757	
5°	731	67
15°	528	146
25°	288	132
35°	126	80
45°	39	32
55°	16	14
65°	8	9
75°	4	5
85°	2	1
90°	0	

TEST NUMBER: P1254277

CATALOG NUMBER: P3AS09R309035DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	757.4
1°	756.6
2°	753.6
3°	748.3
4°	740.8
5°	731.0
6°	718.9
7°	706.1
8°	689.5
9°	670.7
10°	651.1
11°	628.5
12°	604.4
13°	580.3
14°	553.9
15°	528.3
17.5°	461.2
20°	397.9
22.5°	339.1
25°	287.9
27.5°	241.2
30°	199.7
32.5°	161.3
35°	125.9
37.5°	96.5
40°	72.3
42.5°	52.8
45°	39.2
47.5°	29.4
50°	21.9
52.5°	17.3
55°	15.8
57.5°	13.6
60°	12.1
62.5°	9.8
65°	8.3
67.5°	7.5
70°	6.0
72.5°	5.3
75°	4.5
77.5°	3.8
80°	2.3
82.5°	1.5
85°	1.5
87.5°	0.8



TEST NUMBER: P1254277

CATALOG NUMBER: P3AS09R309035DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)