

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254306

Luminaire Tested: P3AS09R359035DE010 E3PH1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1254306  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R359035DE010 E3PH1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3PH1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 874.0 lumens  
Efficiency: N/A  
Efficacy: 78.7 lumens/watt  
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1254306  
CATALOG NUMBER: P3AS09R359035DE010 E3PH1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1254306

CATALOG NUMBER: P3AS09R359035DE010 E3PH1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	631419	631419	631419
5°	620580	619259	617938
10°	568749	551649	538244
15°	407267	394281	389491
20°	188853	195340	202201
25°	44809	63754	66488
30°	13141	15066	16965
35°	3025	4845	4444
40°	658	1288	859
45°	248	248	248
50°	273	0	273
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 288 cd/sqm



TEST NUMBER: P1254306  
 CATALOG NUMBER: P3AS09R359035DE010 E3PH1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	258.5	29.6
10°-20°	462.2	52.9
20°-30°	139.0	15.9
30°-40°	13.3	1.5
40°-50°	0.9	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	859.7	98.4
0°-40°	873.0	99.9
0°-60°	874.0	100.0
0°-90°	874.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	874.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2880	2880	2880	2880	2880	
5°	2819	2818	2813	2810	2807	261
15°	1794	1780	1737	1729	1716	474
25°	185	204	264	275	275	119
35°	11	15	18	20	17	10
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1254306  
 CATALOG NUMBER: P3AS09R359035DE010 E3PH1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2879.5	2879.5	2879.5	2879.5	2879.5
1°	2878.0	2878.0	2876.5	2876.5	2873.5
2°	2871.2	2872.0	2869.0	2868.2	2866.0
3°	2860.7	2858.4	2858.4	2856.9	2855.4
4°	2844.1	2839.6	2838.1	2838.9	2835.9
5°	2819.3	2818.5	2813.3	2809.5	2807.3
6°	2792.2	2786.9	2775.6	2765.9	2763.6
7°	2751.5	2740.3	2730.5	2710.1	2707.1
8°	2701.9	2683.8	2662.7	2634.1	2632.6
9°	2640.9	2611.5	2582.2	2543.8	2530.2
10°	2554.3	2527.2	2477.5	2443.6	2417.3
11°	2446.7	2412.8	2354.8	2314.2	2292.3
12°	2324.7	2293.1	2225.3	2188.4	2157.6
13°	2168.1	2141.8	2078.5	2037.9	2013.8
14°	1986.7	1967.1	1906.9	1888.8	1880.5
15°	1794.0	1780.4	1736.8	1729.2	1715.7
17.5°	1320.4	1297.9	1273.0	1277.5	1282.0
20°	809.3	840.9	837.1	853.7	866.5
22.5°	403.5	444.2	491.6	520.2	534.5
25°	185.2	204.0	263.5	274.8	274.8
27.5°	93.3	97.9	124.2	126.5	132.5
30°	51.9	55.7	59.5	66.2	67.0
32.5°	26.3	30.9	32.4	36.1	34.6
35°	11.3	15.1	18.1	19.6	16.6
37.5°	5.3	6.8	9.8	9.0	6.8
40°	2.3	3.0	4.5	3.8	3.0
42.5°	1.5	1.5	2.3	1.5	1.5
45°	0.8	0.8	0.8	0.8	0.8
47.5°	0.8	0.8	0.0	0.8	0.8
50°	0.8	0.0	0.0	0.0	0.8
52.5°	0.8	0.0	0.0	0.0	0.8
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1254306  
CATALOG NUMBER: P3AS09R359035DE010 E3PH1MW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)