

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255174

Luminaire Tested: P3AS17R509035DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255174
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509035DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 978.0 lumens
Efficiency: N/A
Efficacy: 46.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255174

CATALOG NUMBER: P3AS17R509035DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1255174

CATALOG NUMBER: P3AS17R509035DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	284451
5°	276799
10°	255239
15°	224473
20°	187803
25°	148920
30°	109257
35°	75114
40°	47747
45°	26669
50°	14464
55°	12157
60°	10438
65°	9599
70°	8463
75°	7879
80°	6693
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26669 cd/sqm

TEST NUMBER: P1255174

CATALOG NUMBER: P3AS17R509035DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.5	11.9
10°-20°	273.8	28.0
20°-30°	280.1	28.6
30°-40°	177.6	18.2
40°-50°	70.7	7.2
50°-60°	28.6	2.9
60°-70°	18.3	1.9
70°-80°	9.4	1.0
80°-90°	2.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.4	68.6
0°-40°	848.0	86.7
0°-60°	947.4	96.9
0°-90°	978.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	978.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1297	
5°	1258	116
15°	989	274
25°	616	280
35°	281	178
45°	86	71
55°	32	29
65°	18	18
75°	9	9
85°	3	3
90°	0	

TEST NUMBER: P1255174

CATALOG NUMBER: P3AS17R509035DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1297.2
2.5°	1287.9
5°	1257.5
7.5°	1209.8
10°	1146.3
12.5°	1070.8
15°	988.8
17.5°	898.8
20°	804.8
22.5°	710.8
25°	615.5
27.5°	520.2
30°	431.5
32.5°	352.1
35°	280.6
37.5°	219.7
40°	166.8
42.5°	123.1
45°	86.0
47.5°	58.2
50°	42.4
52.5°	35.7
55°	31.8
57.5°	27.8
60°	23.8
62.5°	21.2
65°	18.5
67.5°	15.9
70°	13.2
72.5°	10.6
75°	9.3
77.5°	6.6
80°	5.3
82.5°	4.0
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)