

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254330

Luminaire Tested: P3AS09R409035DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409035DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 673.0 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254330
CATALOG NUMBER: P3AS09R409035DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1254330
 CATALOG NUMBER: P3AS09R409035DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151084
5°	148338
10°	139833
15°	126993
20°	111566
25°	95280
30°	78924
35°	60873
40°	43310
45°	29181
50°	15931
55°	11240
60°	10569
65°	9755
70°	8719
75°	8303
80°	6693
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29181 cd/sqm



TEST NUMBER: P1254330
 CATALOG NUMBER: P3AS09R409035DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.8	9.3
10°-20°	155.8	23.2
20°-30°	180.2	26.8
30°-40°	142.0	21.1
40°-50°	72.9	10.8
50°-60°	27.9	4.1
60°-70°	18.4	2.7
70°-80°	10.0	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	398.8	59.3
0°-40°	540.8	80.4
0°-60°	641.6	95.3
0°-90°	673.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	673.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	689	
5°	674	63
15°	559	156
25°	394	180
35°	227	142
45°	94	73
55°	29	28
65°	19	18
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1254330
CATALOG NUMBER: P3AS09R409035DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	689.0
2.5°	685.2
5°	673.9
7.5°	654.3
10°	628.0
12.5°	597.1
15°	559.4
17.5°	520.3
20°	478.1
22.5°	435.2
25°	393.8
27.5°	352.4
30°	311.7
32.5°	270.3
35°	227.4
37.5°	187.5
40°	151.3
42.5°	120.5
45°	94.1
47.5°	68.5
50°	46.7
52.5°	33.9
55°	29.4
57.5°	26.4
60°	24.1
62.5°	21.1
65°	18.8
67.5°	15.8
70°	13.6
72.5°	11.3
75°	9.8
77.5°	7.5
80°	5.3
82.5°	4.5
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)