

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255176

Luminaire Tested: P3AS17R559035DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255176
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559035DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1762.9 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255176
CATALOG NUMBER: P3AS17R559035DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1255176
 CATALOG NUMBER: P3AS17R559035DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84			
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	86	83	80	79			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70			
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66			
8	83	74	69	65	82	74	69	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	488974
5°	484436
10°	503887
15°	496893
20°	458213
25°	372820
30°	226465
35°	78380
40°	22385
45°	10668
50°	4503
55°	2026
60°	2324
65°	2075
70°	1667
75°	2203
80°	1642
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10668 cd/sqm



TEST NUMBER: P1255176
 CATALOG NUMBER: P3AS17R559035DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.8	12.1
10°-20°	608.3	34.5
20°-30°	678.2	38.5
30°-40°	221.9	12.6
40°-50°	29.2	1.7
50°-60°	6.2	0.3
60°-70°	3.6	0.2
70°-80°	2.2	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1499.3	85.0
0°-40°	1721.2	97.6
0°-60°	1756.5	99.6
0°-90°	1762.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1762.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2230	
5°	2201	213
15°	2189	608
25°	1541	678
35°	293	222
45°	34	29
55°	5	6
65°	4	4
75°	3	2
85°	0	1
90°	0	



TEST NUMBER: P1255176
CATALOG NUMBER: P3AS17R559035DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2229.9
2.5°	2214.0
5°	2200.8
7.5°	2232.6
10°	2263.0
12.5°	2247.1
15°	2188.8
17.5°	2096.1
20°	1963.6
22.5°	1780.8
25°	1540.9
27.5°	1236.2
30°	894.4
32.5°	548.5
35°	292.8
37.5°	148.4
40°	78.2
42.5°	50.3
45°	34.4
47.5°	23.8
50°	13.2
52.5°	7.9
55°	5.3
57.5°	5.3
60°	5.3
62.5°	4.0
65°	4.0
67.5°	2.6
70°	2.6
72.5°	2.6
75°	2.6
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)