

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254347

Luminaire Tested: P3AS09R459035DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459035DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 842.0 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254347
CATALOG NUMBER: P3AS09R459035DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1254347
 CATALOG NUMBER: P3AS09R459035DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74			
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62			
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	316203
5°	308782
10°	283851
15°	240524
20°	186613
25°	130435
30°	82165
35°	48372
40°	27366
45°	13304
50°	4640
55°	3747
60°	3640
65°	3528
70°	3398
75°	3219
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13304 cd/sqm



TEST NUMBER: P1254347
 CATALOG NUMBER: P3AS09R459035DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.9	15.4
10°-20°	290.9	34.6
20°-30°	247.0	29.3
30°-40°	117.9	14.0
40°-50°	35.5	4.2
50°-60°	9.0	1.1
60°-70°	6.7	0.8
70°-80°	4.0	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	667.8	79.3
0°-40°	785.7	93.3
0°-60°	830.2	98.6
0°-90°	842.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	842.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1442	
5°	1403	130
15°	1060	291
25°	539	247
35°	181	118
45°	43	36
55°	10	9
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1254347
CATALOG NUMBER: P3AS09R459035DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1442.0
2.5°	1433.0
5°	1402.8
7.5°	1350.9
10°	1274.8
12.5°	1173.9
15°	1059.5
17.5°	932.2
20°	799.7
22.5°	664.9
25°	539.1
27.5°	424.7
30°	324.5
32.5°	244.0
35°	180.7
37.5°	133.3
40°	95.6
42.5°	66.3
45°	42.9
47.5°	24.1
50°	13.6
52.5°	10.5
55°	9.8
57.5°	9.0
60°	8.3
62.5°	7.5
65°	6.8
67.5°	6.0
70°	5.3
72.5°	4.5
75°	3.8
77.5°	3.0
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)