

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254354

Luminaire Tested: P3AS09R459035DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1254354  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R459035DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 653.0 lumens  
Efficiency: N/A  
Efficacy: 58.8 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1254354  
CATALOG NUMBER: P3AS09R459035DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1254354  
 CATALOG NUMBER: P3AS09R459035DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	138454
5°	135989
10°	128699
15°	117367
20°	103796
25°	90126
30°	77354
35°	64460
40°	48033
45°	29398
50°	13611
55°	10628
60°	10218
65°	9391
70°	8655
75°	8303
80°	7577
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29398 cd/sqm



TEST NUMBER: P1254354  
 CATALOG NUMBER: P3AS09R459035DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.7	8.8
10°-20°	143.9	22.0
20°-30°	171.0	26.2
30°-40°	148.6	22.8
40°-50°	74.5	11.4
50°-60°	25.9	4.0
60°-70°	18.2	2.8
70°-80°	10.1	1.5
80°-90°	3.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.7	57.1
0°-40°	521.3	79.8
0°-60°	621.6	95.2
0°-90°	653.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	653.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	631	
5°	618	58
15°	517	144
25°	372	171
35°	241	149
45°	95	75
55°	28	26
65°	18	18
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1254354  
CATALOG NUMBER: P3AS09R459035DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	631.4
2.5°	628.4
5°	617.8
7.5°	601.3
10°	578.0
12.5°	549.4
15°	517.0
17.5°	480.9
20°	444.8
22.5°	407.9
25°	372.5
27.5°	338.6
30°	305.5
32.5°	273.9
35°	240.8
37.5°	205.4
40°	167.8
42.5°	130.9
45°	94.8
47.5°	62.5
50°	39.9
52.5°	30.9
55°	27.8
57.5°	25.6
60°	23.3
62.5°	21.1
65°	18.1
67.5°	15.8
70°	13.5
72.5°	11.3
75°	9.8
77.5°	7.5
80°	6.0
82.5°	4.5
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)